

Plug-In Unit Front Panel for Static Trapezoid Handle



The front panel enables the assembly of a plastic or Aluprofile static trapezoid handle. The front panel cannot be shielded with a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, unshielded

Front panel, Al, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Depth (D): 2.5mm

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

Type: Front Panel for Handle (PIU)


Table 1/3						
Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish

30847-602	3U	ЗНР	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-603	3U	4HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-604	3U	5HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-605	3U	6НР	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-625	6U	ЗНР	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-606	3U	7HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-607	3U	8HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-626	6U	4HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-608	3U	10HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-627	6U	5HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-609	3U	12HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-628	6U	6НР	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized

30847-630	6U	8HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-631	6U	10HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized

Table 2/3						
Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)
30847-602	Conductive	No	IEC 60297-3-	No	128.4mm	14.9mm
30847-603	Conductive	No	IEC 60297-3-	No	128.4mm	20mm
30847-604	Conductive	No	IEC 60297-3-	No	128.4mm	25mm
30847-605	Conductive	No	IEC 60297-3-	No	128.4mm	30.1mm
30847-625	Conductive	No	IEC 60297-3-	No	261.8mm	14.9mm
30847-606	Conductive	No	IEC 60297-3-	No	128.4mm	35.2mm
30847-607	Conductive	No	IEC 60297-3-	No	128.4mm	40.3mm
30847-626	Conductive	No	IEC 60297-3-	No	261.8mm	20mm
30847-608	Conductive	No	IEC 60297-3- 101	No	128.4mm	50.5mm
30847-627	Conductive	No	IEC 60297-3-	No	261.8mm	25mm
30847-609	Conductive	No	IEC 60297-3-	No	128.4mm	60.6mm
30847-628	Conductive	No	IEC 60297-3-	No	261.8mm	30.1mm
30847-630	Conductive	No	IEC 60297-3-	No	261.8mm	40.3mm
30847-631	Conductive	No	IEC 60297-3-	No	261.8mm	50.5mm

Tabl	e 3/3
Catalog Number	Quick Ship
30847-602	No
30847-603	No
30847-604	No
30847-605	No
30847-625	No
30847-606	No
30847-607	No
30847-626	No
30847-608	No
30847-627	No
30847-609	No
30847-628	No
30847-630	No
30847-631	No



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE