

Front Panel, Unshielded, Bottom Hinged

Unshielded front panel bottom hinged.



CERTIFICATIONS



FEATURES

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

SPECIFICATIONS

- Depth (D):** 2.5mm
- Material:** Aluminum
- Finish:** Anodized
- Accessory Type:** Front panel
- Product Type:** Front Panel
- Type:** Front Panel without Handle

Table 1/2

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Front Finish | Rear Finish |
|----------------|-------------|------------|------------------|----------------|--------------|-------------|
| 20838-280 | 3U | 28HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-271 | 3U | 42HP | 1 | Hinged, Bottom | Anodized | Conductive |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Mounting | Front Finish | Rear Finish |
|---------------|-------------|------------|------------------|----------------|--------------|-------------|
| 20838-277 | 4U | 42HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-272 | 3U | 63HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-273 | 3U | 84HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-278 | 4U | 63HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-274 | 6U | 42HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-279 | 4U | 84HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-275 | 6U | 63HP | 1 | Hinged, Bottom | Anodized | Conductive |
| 20838-276 | 6U | 84HP | 1 | Hinged, Bottom | Anodized | Conductive |

Table 2/2


| Catalog Number | Treated Edges | Complies With | EMC Shielding | Height (H) | Width (W) | Quick Ship |
|----------------|---------------|---------------------------------|---------------|------------|-----------|------------|
| 20838-280 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 128.4mm | 141.9mm | No |
| 20838-271 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 128.4mm | 213mm | No |
| 20838-277 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 172.9mm | 213mm | No |
| 20838-272 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 128.4mm | 319.7mm | No |
| 20838-273 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 128.4mm | 426.4mm | No |
| 20838-278 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 172.9mm | 319.7mm | No |
| 20838-274 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 261.8mm | 213mm | No |

| CatalogNumber | Treated Edges | Complies With | EMC Shielding | Height (H) | Width (W) | Quick Ship |
|---------------|---------------|---------------------------------|---------------|------------|-----------|------------|
| 20838-279 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 172.9mm | 426.4mm | No |
| 20838-275 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 261.8mm | 319.7mm | No |
| 20838-276 | No | IEC 60297-3-101, IEEE 1101.1/10 | No | 261.8mm | 426.4mm | No |

ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position (> 135°).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE