


# Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Bottom, 10 Pieces


## CATALOG NUMBER

**20817-660**



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

## CERTIFICATIONS



## FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

With locking

Codeable i.a.w. IEEE 1101.10 and IEC 60297-3-103

Package Quantity: 10

Flammability Rating: UL® 94V-0

Complies With: EN 45545-2

Product Type: Handle

Works With: Front Panels

Gross Weight: 0.235kg

Please order Coding pegs and Microswitch separately.

Technical drawing of a door handle assembly. The drawing includes an exploded view of the handle and a detailed view of the handle body with dimensions. The exploded view shows the handle being attached to a door plate. The detailed view of the handle body includes the following dimensions:

- Overall width: 26
- Overall height: 45
- Mounting hole diameter:  $\varnothing 2.85$
- Mounting hole offset from bottom: 8.95
- Mounting hole offset from side: 12.75
- Handle body width: 22.75
- Handle body offset from side: 2.5
- Handle body offset from top: 14
- Handle body offset from side (inner): 6.1
- Handle body offset from side (outer): 3.6
- Handle body offset from side (inner): 2.5
- Handle body offset from side (outer): 3.8
- Handle body offset from side (inner): 8.15
- Handle body offset from side (outer): 8.95
- Handle body offset from side (inner): 2.5
- Handle body offset from side (outer): 3.6
- Handle body offset from side (inner): 6.1
- Handle body offset from side (outer): 2.5

The exploded view shows the handle being attached to a door plate. The handle is shown in two positions: one where it is being inserted into the door plate and another where it is fully inserted. The door plate has a mounting hole with a diameter of 4.07. The handle has a mounting hole with a diameter of 2.85. The handle is shown in two positions: one where it is being inserted into the door plate and another where it is fully inserted. The door plate has a mounting hole with a diameter of 4.07. The handle has a mounting hole with a diameter of 2.85.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**