


AdvancedTCA Air Deflector Filler Panel



Advanced TCA front panels cover empty slots in a system. The additional air baffle blocks and guide the air in the right direction.

CERTIFICATIONS



FEATURES

Front panels cover empty slots in a system, 8 U, 6 HP

SPECIFICATIONS

Rack Width:	6HP
Height (H):	350.78mm
Product Family:	AdvancedTCA
Type:	Front Panel
Product Type:	Front Panel
Works With:	Systems

Table 1/3

Catalog Number	Material	Finish	Package Quantity	Mounting	Gasket Type	Front Finish
21591-104	Aluminum	Passivated	1	Screw-on Front	Textile EMC	Raw
21591-097	Stainless Steel		1	Screw-on Front	Textile EMC	Raw

Table 2/3

Catalog Number	Rear Finish	Accessory Type	Depth (D)	EMC Shielding	Rack Height	Width (W)
21591-104	Raw	Front panel	2.5mm	Yes	8U	30.14mm
21591-097	Raw	Front panel	1mm	Yes	8U	28.95mm

Table 3/3

Catalog Number	Quick Ship
21591-104	No
21591-097	No

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE