

Insertor/Extractor Handle Type IEL, Black Lever, Grey Button, Bottom; 10 pieces

CATALOG NUMBER

20817-682



The inserter/extractor handle, type IEL in accordance with IEEE 1101.10. 0,1" offset Two of these handles can overcome a single lever force of 700N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

0.1" offset is used for PSUs with SMD Plus

PRODUCT ATTRIBUTES

Package Quantity: 10

Handle Type: IEL; Bottom Front

Color: Jet Black

Complies With: EN 45545-2

Height (H): 25.5mm

Product Type: Handle

Width (W): 19.8mm

Gross Weight: 0.253kg

Please order Coding pegs and Microswitch separately.

Technical drawing of the front door assembly, showing side, top, and bottom views with dimensions in mm.

Side View Dimensions:

- Top flange width: 2.5
- Top flange height: 6.1
- Top flange thickness: 3.6
- Main body width: 35
- Main body height: 26
- Bottom flange width: 2.5
- Bottom flange height: 3.8
- Bottom flange thickness: 8.55
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 8.15
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 12.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 22.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 2.5

Top View Dimensions:

- Top flange width: 2.5
- Top flange height: 6.1
- Top flange thickness: 3.6
- Main body width: 35
- Main body height: 26
- Bottom flange width: 2.5
- Bottom flange height: 3.8
- Bottom flange thickness: 8.55
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 8.15
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 12.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 22.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 2.5

Bottom View Dimensions:

- Top flange width: 2.5
- Top flange height: 6.1
- Top flange thickness: 3.6
- Main body width: 35
- Main body height: 26
- Bottom flange width: 2.5
- Bottom flange height: 3.8
- Bottom flange thickness: 8.55
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 8.15
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 12.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 22.75
- Bottom flange hole diameter: $\varnothing 2.65$
- Bottom flange hole offset: 2.5

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE