


# Test Adaptor for VMEbus



Test Adapter for VMEbus Boards to access test points on the board.

## CERTIFICATIONS



## FEATURES

Routing and layer stack-up match the requirements of the VME bus

Measuring field for current and voltage measurement (V/I), (a)

Additional measuring pins, e.g. for the probe tips of an oscilloscope (b)

1 pin position for second test object, 1 pin position for terminator board

6 U test adaptors consist of two 3 U test adaptors linked via an intermediate adaptor

Voltage supply lines are designed for 2 A

## SPECIFICATIONS

Table 1/2

| Catalog Number | Type   | Connector Type                | Board Depth | Rack Height | Measuring Field  | Number of Layers |
|----------------|--------|-------------------------------|-------------|-------------|------------------|------------------|
| 23022-002      | VMEbus | C96, System Bus, C96, I/O Bus | 160mm       | 6U          | Current, Voltage | 6                |
| 23021-002      | VMEbus | C96, System Bus               | 220mm       | 3U          | Current, Voltage | 6                |

| CatalogNumber | Type   | ConnectorType                 | Board Depth | Rack Height | MeasuringField   | Number of Layers |
|---------------|--------|-------------------------------|-------------|-------------|------------------|------------------|
| 23021-100     | VMEbus | C96, I/O Bus                  | 160mm       | 3U          | Current, Voltage | 6                |
| 23021-001     | VMEbus | C96, System Bus               | 160mm       | 3U          | Current, Voltage | 6                |
| 23021-101     | VMEbus | C96, I/O Bus                  | 220mm       | 3U          | Current, Voltage | 6                |
| 23022-010     | VMEbus | C96, System Bus, C96, I/O Bus | 280mm       | 6U          | Current, Voltage | 6                |
| 23022-004     | VMEbus | C96, System Bus, C96, I/O Bus | 220mm       | 6U          | Current, Voltage | 6                |

Table 2/2

| Catalog Number | Package Quantity | Quick Ship |
|----------------|------------------|------------|
| 23022-002      | 1                | No         |
| 23021-002      | 1                | No         |
| 23021-100      | 1                | No         |
| 23021-001      | 1                | No         |
| 23021-101      | 1                | No         |
| 23022-010      | 1                | No         |
| 23022-004      | 1                | No         |

## ADDITIONAL PRODUCT DETAILS

For 9 U VMEbus test Adapter solution see Intermediate Adaptor Adaptor Bracket, 9 U, 220 mm, 350 mm.

P1 = System Bus, P2 = I/O Bus.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**