


Front Panel, Shielded, Bottom Hinged

Power Utilities

U-profile front panel bottom hinged for textile gasket.



CERTIFICATIONS



FEATURES

U-profile front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

Shielded, U front panel with textile EMC gasket

Suitable for subracks (EuropacPRO) and cases (RatiopacPRO, PropacPRO, CompacPRO)

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20848-599	3 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20848-600	3 U	63 HP	1	Hinged, Bottom	Anodized	Conductive

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20848-601	3 U	84 HP	1	Hinged, Bottom	Anodized	Conductive
20848-602	6 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20848-603	6 U	63 HP	1	Hinged, Bottom	Anodized	Conductive
20848-604	6 U	84 HP	1	Hinged, Bottom	Anodized	Conductive
20848-605	4 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20848-606	4 U	63 HP	1	Hinged, Bottom	Anodized	Conductive
20848-607	4 U	84 HP	1	Hinged, Bottom	Anodized	Conductive
20848-608	3 U	28 HP	1	Hinged, Bottom	Anodized	Conductive
20848-696	6 U	28 HP	1	Hinged, Bottom	Anodized	Conductive

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Height	Material	Product Type
20848-599	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminum	Front Panel
20848-600	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminum	Front Panel
20848-601	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminum	Front Panel
20848-602	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminum	Front Panel
20848-603	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminum	Front Panel
20848-604	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminum	Front Panel

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Height	Material	Product Type
20848-605	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminum	Front Panel
20848-606	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminum	Front Panel
20848-607	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminum	Front Panel
20848-608	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminum	Front Panel
20848-696	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminum	Front Panel

Table 3/3

Catalog Number	Type	Width
20848-599	Front Panel without Handle	213 mm
20848-600	Front Panel without Handle	319.7 mm
20848-601	Front Panel without Handle	426.4 mm
20848-602	Front Panel without Handle	213 mm
20848-603	Front Panel without Handle	319.7 mm
20848-604	Front Panel without Handle	426.4 mm
20848-605	Front Panel without Handle	213 mm
20848-606	Front Panel without Handle	319.7 mm
20848-607	Front Panel without Handle	426.4 mm
20848-608	Front Panel without Handle	141.9 mm
20848-696	Front Panel without Handle	141.9 mm

ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position (> 135°).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE