

InterSafe Data Interface Port for Profibus



InterSafe Data Interface Port allows programming access to devices inside without opening the enclosure door, reducing the risk of exposing to energized components. Many configurations are standard and ready-to-use to meet various applications and programming requirements.

FEATURES

Steel and Stainless Steel doors are welded and ground

Back plate is aluminum

All standard configurations include a GFCI or standard duplex receptacle with a 5-A circuit breaker for added safety

Door gasket (between the door and plate assemblies) and plate gasket (between the plate assembly and the enclosure) together provide a tight seal

Template provided for accurate enclosure cutout dimensions

Quarter-turn latch with screwdriver slot and padlock hasp on all steel and stainless steel door models for convenience and security

Quarter-turn latch with screwdriver slot on polycarbonate models

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Thickness	Configuration
HGF5PBSS	15952	Stainless Steel 304	Brushed		1.5mm	120 VAC GFCI Receptacle, 9-pin Profibus, 5-amp Circuit Breaker
HDP5PBCC	16184	Polycarbonate	Smooth Matte		1.5mm	120 VAC Duplex Receptacle, 9-pin Profibus, 5-amp Circuit Breaker
HGF5PB	14784	Mild Steel	Powder Coated	Black	1.5mm	120 VAC GFCI Receptacle, 9-pin Profibus, 5-amp Circuit Breaker
HDP5PB	14932	Mild Steel	Powder Coated	Black	1.5mm	120 VAC Duplex Receptacle, 9-pin Profibus, 5-amp Circuit Breaker

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN TRACHTE ILSCO SCHROFF