

# nVent CADDY Speed Link SLK with Loop



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

## SPECIFICATIONS

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Static Load Safety Factor:</b> | 5:1                            |
| <b>Finish:</b>                    | Electrogalvanized              |
| <b>Material:</b>                  | Steel;Polypropylene;Zinc Alloy |
| <b>Complies With:</b>             | SMACNA HVAC-DCS                |

Table 1/2

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Length (L) | Height (H) | Width (W) |
|----------------|----------------|--------------------|------------------|------------|------------|-----------|
|----------------|----------------|--------------------|------------------|------------|------------|-----------|


|             |        |        |     |         |       |       |
|-------------|--------|--------|-----|---------|-------|-------|
| SLK15L10LP  | 196603 | 1.5 mm | 10m | 101.6mm | 55 mm | 19 mm |
| SLK15L1LP   | 196601 | 1.5 mm | 1m  | 101.6mm | 55 mm | 19 mm |
| SLK15L1LPR2 | 196628 | 1.5 mm | 1m  | 101.6mm | 55 mm | 19 mm |
| SLK15L2LP   | 196514 | 1.5 mm | 2m  | 101.6mm | 55 mm | 19 mm |
| SLK15L2LPR2 | 196629 | 1.5 mm | 2m  | 101.6mm | 55 mm | 19 mm |
| SLK15L3LP   | 196515 | 1.5 mm | 3m  | 101.6mm | 55 mm | 19 mm |
| SLK15L3LPR2 | 196630 | 1.5 mm | 3m  | 101.6mm | 55 mm | 19 mm |
| SLK15L5LP   | 196516 | 1.5 mm | 5m  | 101.6mm | 55 mm | 19 mm |
| SLK15L5LPR2 | 196631 | 1.5 mm | 5m  | 101.6mm | 55 mm | 19 mm |
| SLK15L7LP   | 196602 | 1.5 mm | 7m  | 101.6mm | 55 mm | 19 mm |
| SLK2L10LP   | 196606 | 2 mm   | 10m | 101.6mm | 55 mm | 19 mm |
| SLK2L1LP    | 196604 | 2 mm   | 1m  | 101.6mm | 55 mm | 19 mm |
| SLK2L2LP    | 196543 | 2 mm   | 2m  | 101.6mm | 55 mm | 19 mm |
| SLK2L3LP    | 196544 | 2 mm   | 3m  | 101.6mm | 55 mm | 19 mm |
| SLK2L5LP    | 196545 | 2 mm   | 5m  | 101.6mm | 55 mm | 19 mm |
| SLK2L7LP    | 196605 | 2 mm   | 7m  | 101.6mm | 55 mm | 19 mm |
| SLK3L10LP   | 196711 | 3 mm   | 10m | 101.6mm | 62 mm | 24 mm |
| SLK3L1LP    | 196706 | 3 mm   | 1m  | 101.6mm | 62 mm | 24 mm |
| SLK3L2LP    | 196707 | 3 mm   | 2m  | 101.6mm | 62 mm | 24 mm |

|          |        |      |    |         |       |       |
|----------|--------|------|----|---------|-------|-------|
| SLK3L3LP | 196708 | 3 mm | 3m | 101.6mm | 62 mm | 24 mm |
| SLK3L5LP | 196709 | 3 mm | 5m | 101.6mm | 62 mm | 24 mm |

| Table 2/2      |                |               |           |             |                 |
|----------------|----------------|---------------|-----------|-------------|-----------------|
| Catalog Number | Article Number | Thickness (T) | Angle (a) | Static Load | Certifications  |
| SLK15L10LP     | 196603         | 12.5 mm       | 90 ° Max  | 195N        | cUL, UL, SMACNA |
| SLK15L1LP      | 196601         | 12.5 mm       | 90 ° Max  | 195N        | UL, SMACNA, cUL |
| SLK15L1LPR2    | 196628         | 12.5 mm       | 90 ° Max  | 195N        | cUL, UL, SMACNA |
| SLK15L2LP      | 196514         | 12.5 mm       | 90 ° Max  | 195N        | UL, cUL, SMACNA |
| SLK15L2LPR2    | 196629         | 12.5 mm       | 90 ° Max  | 195N        | SMACNA, UL, cUL |
| SLK15L3LP      | 196515         | 12.5 mm       | 90 ° Max  | 195N        | cUL, UL, SMACNA |
| SLK15L3LPR2    | 196630         | 12.5 mm       | 90 ° Max  | 195N        | SMACNA, cUL, UL |
| SLK15L5LP      | 196516         | 12.5 mm       | 90 ° Max  | 195N        | UL, cUL, SMACNA |
| SLK15L5LPR2    | 196631         | 12.5 mm       | 90 ° Max  | 195N        | SMACNA, UL, cUL |
| SLK15L7LP      | 196602         | 12.5 mm       | 90 ° Max  | 195N        | UL, SMACNA, cUL |
| SLK2L10LP      | 196606         | 12.5 mm       | 90 ° Max  | 440N        | UL, SMACNA, cUL |
| SLK2L1LP       | 196604         | 12.5 mm       | 90 ° Max  | 440N        | cUL, SMACNA, UL |
| SLK2L2LP       | 196543         | 12.5 mm       | 90 ° Max  | 440N        | cUL, UL, SMACNA |
| SLK2L3LP       | 196544         | 12.5 mm       | 90 ° Max  | 440N        | UL, cUL, SMACNA |
| SLK2L5LP       | 196545         | 12.5 mm       | 90 ° Max  | 440N        | UL, cUL, SMACNA |
| SLK2L7LP       | 196605         | 12.5 mm       | 90 ° Max  | 440N        | UL, SMACNA, cUL |

| Catalog Number | Article Number | Thickness (T) | Angle (a) | Static Load | Certifications |
|----------------|----------------|---------------|-----------|-------------|----------------|
| SLK3L10LP      | 196711         | 16 mm         | 90 ° Max  | 890N        | SMACNA         |
| SLK3L1LP       | 196706         | 16 mm         | 90 ° Max  | 890N        | SMACNA         |
| SLK3L2LP       | 196707         | 16 mm         | 90 ° Max  | 890N        | SMACNA         |
| SLK3L3LP       | 196708         | 16 mm         | 90 ° Max  | 890N        | SMACNA         |
| SLK3L5LP       | 196709         | 16 mm         | 90 ° Max  | 890N        | SMACNA         |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

