

# EDT2 Enhanced DIN Rail Surge Protection Class II, 3+1 Mode



## CERTIFICATIONS



## FEATURES

Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions

Enhanced temporary over voltage (TOV) withstand capability

External back-up fuse is not required up to 315 A (IEC only)

Compact, yet high surge rated pluggable design, using minimum DIN rail width

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


## SPECIFICATIONS

| Catalog Number                           | EDT230031R              |
|------------------------------------------|-------------------------|
| Nominal System Voltage (Un)              | 240 V                   |
| Max Continuous Operating Voltage (Uc)    | 300 V L-N<br>305 V N-PE |
| Nominal Discharge Current (In), IEC, L-N | 20kA 8/20 $\mu$ s       |

| Catalog Number                                     | EDT230031R                                                                           |
|----------------------------------------------------|--------------------------------------------------------------------------------------|
| Nominal Discharge Current (In), IEC, N-PE          | 40kA 8/20 µs                                                                         |
| Max Discharge Current (Imax), IEC, L-N             | 50kA 8/20 µs                                                                         |
| Max Discharge Current (Imax), IEC, N-PE            | 65kA 8/20 µs                                                                         |
| Voltage Protection Level (Up), L-N                 | 1650V                                                                                |
| Voltage Protection Level (Up), N-PE                | 1500V                                                                                |
| Back-Up Fuse @ Isccr                               | 250 A @ 50 kA<br>315 A @ 25 kA                                                       |
| Frequency                                          | 50 - 60 Hz                                                                           |
| Response Time, L-N                                 | 25 ns Max                                                                            |
| Response Time, N-PE                                | 100 ns Max                                                                           |
| Protection Modes                                   | L-N<br>N-PE                                                                          |
| Short Circuit Current Rating (Isccr)               | 25kA<br>50kA                                                                         |
| Temporary Over Voltage 120 min (Ut/mode), L-N      | 442 V Withstand                                                                      |
| Temporary Over Voltage Withstand 200 ms (Ut), N-PE | 1200V                                                                                |
| Nominal Discharge Current (In), UL                 | 20kA 8/20 µs                                                                         |
| Short Circuit Current Rating (SCCR)                | 150kA                                                                                |
| Voltage Protection Rating (VPR), L-N               | 1200V                                                                                |
| Voltage Protection Rating (VPR), N-PE              | 1000V                                                                                |
| Technology                                         | Thermal Disconnect                                                                   |
| Connection, Solid                                  | 35 mm² Max                                                                           |
| Connection, Stranded                               | 25 mm² Max                                                                           |
| Torque (TQ)                                        | 4.5 N·m                                                                              |
| Humidity                                           | 5 - 95                                                                               |
| Temperature                                        | -35 to 85 °C                                                                         |
| Enclosure Material                                 | UL® 94V-0 Thermoplastic                                                              |
| Enclosure Rating                                   | IP 20                                                                                |
| Mounting                                           | 35 mm top hat DIN rail                                                               |
| Remote Contact Switching Capacity                  | 1 A @ 250 VAC<br>1 A @ 125 VAC<br>0.5 A @ 48 VDC<br>0.5 A @ 24 VDC<br>0.5 A @ 12 VDC |
| Remote Contacts                                    | Yes                                                                                  |
| Status Indication                                  | Mechanical flag                                                                      |

|                       |                                              |
|-----------------------|----------------------------------------------|
| Catalog Number        | EDT230031R                                   |
| Depth (D)             | 69mm                                         |
| Height (H)            | 90 mm                                        |
| Width (W)             | 72 mm                                        |
| Unit Weight           | 0.37 kg                                      |
| Certification Details | UL® 1449 Edition 5 Type 1CA                  |
| Complies With         | EN 61643-11 Type 2<br>IEC® 61643-11 Class II |
| Replacement Module    | SGT240M<br>EDT2300M                          |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE