

## **Fusion G7 Gland Plate**



Provides a removable cable egress and entry plate while maintaining IP/UL/CSA integrity of the enclosure. Maintains IP55 or IP66/UL/CSA Type 4 and 12 when properly installed on a nVent HOFFMAN enclosure.

## **FEATURES**

Foam-in-place gasket, fasteners and instructions provided

## **SPECIFICATIONS**

Color: Light Gray Material: Mild Steel Finish: **Powder Coated** Color Code: RAL 7035

Table 1/1			
Catalog Number	Thickness	Cutout Size	Quick Ship
FUGP1815C500S	1.5mm	150 x 180mm	No
FUGP2809C500S	1.5mm	90 x 280mm	No
FUGP2815C500S	1.5mm	150 x 280mm	No
FUGP1809C500S	1.5mm	90 x 180mm	No

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF**