

Speedway Cable Ladder Equal Cross



CERTIFICATIONS



FEATURES

Creates a four way intersection for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

SPECIFICATIONS

Finish: Hot-Dip Galvanized

Material: Steel

Table 1/2


Catalog Number	Article Number	Width (W)	A	B	C	D
----------------	----------------	-----------	---	---	---	---

CL110X150ECH D	840800	150 mm	900 mm	530 mm	771 mm	80 mm
CL110X300ECH D	840810	300 mm	1050 mm	530 mm	983 mm	80 mm
CL110X450ECH D	840820	450 mm	1200 mm	530 mm	1195 mm	80 mm
CL110X600ECH D	840830	600 mm	1350 mm	530 mm	1407 mm	80 mm
CL110X750ECH D	840840	750 mm	1500 mm	530 mm	1619 mm	80 mm
CL110X900ECH D	840850	900 mm	1650 mm	530 mm	1831 mm	80 mm

Table 2/2

Catalog Number	Article Number	E
CL110X150ECHD	840800	110 mm
CL110X300ECHD	840810	110 mm
CL110X450ECHD	840820	110 mm
CL110X600ECHD	840830	110 mm
CL110X750ECHD	840840	110 mm
CL110X900ECHD	840850	110 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

