


Disconnecting Link with Enclosure for Tape



FEATURES

Allows for quick and easy disconnection of the earthing system to facilitate testing of the earth in isolation

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

Includes stainless steel 304 enclosure, rubber dustproof, halogen-free polyamide insulators, stainless steel hardware

Rubber gland for tape connection

8 microns tinned finish according to ASTM B545 Service Class "C" for corrosive environments

SPECIFICATIONS

Table 1/3

Catalog Number	Material	Finish	A	B	C	Height (H)
DLTBX253404	Stainless Steel 304 (EN 1.4301), Tinned Copper		100 mm	42 mm	16 mm	61.5 mm
DLCBX253404	Stainless Steel 304 (EN 1.4301), Copper	Bare	100 mm	42 mm	16 mm	61.5 mm

Table 2/3

Catalog Number	Thickness (T)	Thread Size (TS)	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)
DLTBX253404	4 mm	M8	125 mm	170 mm	150mm	110 mm
DLCBX253404	4 mm	M8	125 mm	170 mm	150mm	110 mm


Table 3/3

Catalog Number	Width 1 (W1)	Width 2 (W2)	Width 3 (W3)	Unit Weight
DLTBX253404	40 mm	150 mm	170mm	1.19 kg
DLCBX253404	40 mm	150 mm	170mm	1.19 kg

ADDITIONAL PRODUCT DETAILS

Available tape size 25 x 3 mm to 40 x 4 mm.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE