


# Plug-In Unit U-Profile Front Panel for Handle Form 1



U-profile front panel. Enables the assembly of form 1 trapezoid form extraction handle. The front panel can be shielded with a textile gasket.

## CERTIFICATIONS



## FEATURES

Al profile, front anodized, rear conductive

Front panel, U-profile, shieldable

Alignment pin pressed-in, stainless steel

## SPECIFICATIONS

|                        |                               |
|------------------------|-------------------------------|
| <b>Material:</b>       | Aluminum                      |
| <b>Finish:</b>         | Anodized; Passivated          |
| <b>Accessory Type:</b> | Front panel                   |
| <b>Product Type:</b>   | Front Panel                   |
| <b>Type:</b>           | Front Panel with Handle (PIU) |
| <b>EMC Shielding:</b>  | No (Retrofittable)            |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Handle Type | Mounting | Gasket Type |
|----------------|-------------|------------|------------------|-------------|----------|-------------|
|----------------|-------------|------------|------------------|-------------|----------|-------------|

|           |    |      |   |                   |                |             |
|-----------|----|------|---|-------------------|----------------|-------------|
| 30848-461 | 3U | 4HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-463 | 3U | 6HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-465 | 3U | 8HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-468 | 6U | 4HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-466 | 3U | 10HP | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-467 | 3U | 12HP | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-470 | 6U | 6HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-472 | 6U | 8HP  | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-473 | 6U | 10HP | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |
| 30848-474 | 6U | 12HP | 1 | Trapezoid, Type 1 | Screw-on Front | Textile EMC |

Table 2/3

| Catalog Number | Front Finish | Rear Finish | Treated Edges | Complies With                   | Depth (D) | Height (H) |
|----------------|--------------|-------------|---------------|---------------------------------|-----------|------------|
| 30848-461      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 128.4mm    |
| 30848-463      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 128.4mm    |
| 30848-465      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 128.4mm    |
| 30848-468      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    |
| 30848-466      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 128.4mm    |
| 30848-467      | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 128.4mm    |

| CatalogNumber | Front Finish | Rear Finish | Treated Edges | Complies With                   | Depth (D) | Height (H) |
|---------------|--------------|-------------|---------------|---------------------------------|-----------|------------|
| 30848-470     | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    |
| 30848-472     | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    |
| 30848-473     | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    |
| 30848-474     | Anodized     | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    |

Table 3/3


| Catalog Number | Width (W) | Quick Ship |
|----------------|-----------|------------|
| 30848-461      | 20mm      | No         |
| 30848-463      | 30.1mm    | No         |
| 30848-465      | 40.3mm    | No         |
| 30848-468      | 20mm      | No         |
| 30848-466      | 50.5mm    | No         |
| 30848-467      | 60.6mm    | No         |
| 30848-470      | 30.1mm    | No         |
| 30848-472      | 40.3mm    | No         |
| 30848-473      | 50.5mm    | No         |
| 30848-474      | 60.6mm    | No         |

## ADDITIONAL PRODUCT DETAILS

Please order EMC profile seal separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

## Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

## Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

## Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE