

DT2 DIN Rail Surge Protection Class II, 3+0 Mode



CERTIFICATIONS



FEATURES

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


SPECIFICATIONS

Catalog Number	DT230030R	DT235030R	DT248030R
Nominal System Voltage (Un)	240 V	277 V	400 V
Max Continuous Operating Voltage (Uc)	300 V	350 V	480 V
Nominal Discharge Current (In), IEC	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Max Discharge Current (Imax), IEC	50kA 8/20 μ s	50kA 8/20 μ s	50kA 8/20 μ s

Catalog Number	DT230030R	DT235030R	DT248030R
Voltage Protection Level (Up)	1500V	1750V	2300V
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz	50 - 60 Hz	50 - 60 Hz
Response Time	25 ns Max	25 ns Max	25 ns Max
Protection Modes	L-PEN	L-PEN	L-PEN
Short Circuit Current Rating (Isccr)	25kA 50kA	25kA 50kA	25kA 50kA
Temporary Over Voltage 120 min (Ut/mode)	442 V Safe Fail	529 V Withstand	762 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	337V	403V	581V
Nominal Discharge Current (In), UL	20kA 8/20 µs	20kA 8/20 µs	20kA 8/20 µs
Short Circuit Current Rating (SCCR)	150kA	200kA	200kA
Voltage Protection Rating (VPR)	900V	1000V	1500V
Technology	Thermal Disconnect	Thermal Disconnect	Thermal Disconnect
Connection, Solid	35 mm² Max	35 mm² Max	35 mm² Max
Connection, Stranded	25 mm² Max	25 mm² Max	25 mm² Max
Torque (TQ)	4.5 N·m	4.5 N·m	4.5 N·m
Humidity	5 - 95	5 - 95	5 - 95
Temperature	-35 to 85 °C	-35 to 85 °C	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC
Remote Contacts	Yes	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag	Mechanical flag
Depth (D)	69mm	69mm	69mm
Height (H)	90 mm	90 mm	90 mm
Width (W)	54 mm	54 mm	54 mm
Unit Weight	0.38 kg	0.39 kg	0.41 kg

Catalog Number	DT230030R	DT235030R	DT248030R
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 2 IEC® 61643-11 Class II	EN 61643-11 Type 2 IEC® 61643-11 Class II	EN 61643-11 Type 2 IEC® 61643-11 Class II
Replacement Module	DT2300M	DT2350M	DT2480M

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE