

# Heat Shrink Insulation, Straight



## FEATURES

Heat shrink tubing for insulating connections

## SPECIFICATIONS

<b>Conductor Size, UL:</b>	0.35" - 0.94"
<b>Shrink Ratio:</b>	4:1
<b>Color:</b>	Black
<b>Material:</b>	Polyolefin

Table 1/1


Catalog Number	Expanded Diameter	Recovered Diameter	Length (L)	Diameter (Ø)	Dielectric Strength	Temperature
A130AE	33.27 mm Min	8 mm Max	1219.2mm	38.1 mm	430	-18 to 90 °C
A130AEWTB01	33.27 mm Min	8 mm Max	152.4mm	38.1 mm	430	-18 to 90 °C

## ADDITIONAL PRODUCT DETAILS

Recovered Diameter refers to the final inner diameter of the tubing after the tubing has been fully shrunk, or recovered, through the careful application of heat. A maximum value is specified to ensure the tubing will fit tightly around the object being covered.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**