

# Cable to Web of Rail T20 Complete Welder Pair, Power, UIC, 95 mm<sup>2</sup> Ropelay

## Data Solutions

### CATALOG NUMBER

**PBWT20X5**



### FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Each part number Includes both right and left hand welders

Includes mold cleaner and flint ignitor

### PRODUCT ATTRIBUTES

Material: Graphite; Steel; Thermoplastic

Rail Type: UIC

Bond Terminal Style: W

Conductor Size: 95 mm<sup>2</sup> Ropelay

Conductor Outer Diameter, Nominal: 15.52mm

Welder Style: T20

Mold Only: No

Replacement Mold: PBWX5

Welding Material: PB90, Sold Separately

Handle Clamp: C105C, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**