


nVent ERICO Cadweld Exolon, Busbar to Busbar




Developed in 1988, nVent ERICO Cadweld Exolon connections represented a significant advancement in welded electrical connections for sensitive indoor applications like data centers, hospitals, and other clean room environments. The virtual elimination of smoke and a unique electronic starting system makes this an ideal solution for sensitive applications. Each nVent ERICO Cadweld Exolon package contains ceramic filters that produce an extremely low emission connection.

CERTIFICATIONS



DIAGRAMS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

SPECIFICATIONS

Table 1/1

| Catalog Number | Mold Family | Lug/Busbar Size 1 | Lug/Busbar Size 2 | Certifications |
|----------------|-------------|-------------------|-------------------|----------------|
|----------------|-------------|-------------------|-------------------|----------------|

| | | | | |
|--------------|----|--------------|--------------|---------|
| XLBACCAJ | BA | 3 mm x 25 mm | 3 mm x 25 mm | UL, cUL |
| XLBFDCAJPAM | BF | 3 mm x 25 mm | 6 mm x 50 mm | |
| XLBFDCAJPAMS | BF | 3 mm x 25 mm | 6 mm x 50 mm | |
| XLBQCCAJCAJ | BQ | 3 mm x 25 mm | 3 mm x 25 mm | |
| XLBQCCAJPAM | BQ | 3 mm x 25 mm | 6 mm x 50 mm | |
| XLBQCCAJPAMS | BQ | 3 mm x 25 mm | 6 mm x 50 mm | |

ADDITIONAL PRODUCT DETAILS

A gap between conductors may be required. See mold tag for more information.

| XL-XX-X-XX-XX-L-M-W | | |
|---------------------|----------------------------------|---|
| XL | ERICO CADWELD EXOLON Designation | |
| XX | Mold Family | |
| X | Price Key | |
| XX | Lug/Busbar Size 1 | |
| XX | Lug/Busbar Size 2 | |
| L* | Split Crucible | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M* | Mold Only | |
| W* | Wear Plates | Reduce mechanical abrasion of molds at cable entry points |

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE