

# Compact Axial Fans



Compact Cooling Fans are ideal for applications where enclosure space is limited and quiet, reliable cooling is required. Engineered for 50,000 hours of continuous operation without lubrication or service.

## INDUSTRY STANDARDS

---

UL Component Recognized

## FEATURES

---

Maximum operating temperature is 158 F (70 C)

4-inch fan is thermally protected and uses permanently lubricated ball bearings

6- and 10-inch fans have ball-bearing construction and split-capacitor motors

Split-capacitor motors are thermally protected to avoid premature failure

Dynamically balanced impellers molded from polycarbonate material

One finger guard is furnished (additional finger guards are available)

All mounting hardware is provided

240 and 560 CFM fans have ball bearing construction and split capacitor motors

Fans have leadwires with ends stripped 1/2-inch (12-mm) or 6-foot (1.8-m) cord with polarized plug for power connections

Fan bracket and additional finger guards must be purchased separately

## SPECIFICATIONS

**Color:** Jet Black  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

Catalog Number	Article Number	Airflow	Nominal Voltage	Height	Width	Depth
A2AXFN24	17393	36m³/h	24V	60mm	117mm	25mm
A3AXFN	17395	46m³/h	115V	80mm	117mm	38mm
A4AXFNGQ	13852	83m³/h	115V	117mm	117mm	44mm
A3AXFN24	17394	69m³/h	24V	80mm	117mm	38mm
A4AXFN2	22120	170m³/h	230V	117mm	117mm	44mm
A6AXFNGQ	13853	173m³/h	115V	149mm	149mm	57mm
A6AXFN2	22130	173m³/h	230V	149mm	149mm	57mm
A4AXFN	22210	170m³/h	115V	117mm	117mm	44mm
A4AXFNPG	50429	170m³/h	115V	117mm	117mm	44mm
A4AXFN24	17391	200m³/h	24V	117mm	117mm	44mm
A6AXFN	22220	407m³/h	115V	149mm	149mm	57mm
A6AXFNPG	50439	407m³/h	115V	149mm	149mm	57mm
A10AXFN2	22140	951m³/h	230V	229mm	229mm	95mm
A6AXFN24	17392	476m³/h	24V	149mm	149mm	57mm
A10AXFN	22230	951m³/h	115V	229mm	229mm	95mm
A10AXFNPG	50449	951m³/h	115V	229mm	229mm	95mm

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**