


# Swing Frame Transversal Support Bars, ESFB



The support bars allow for partial or full height swing frame mounting and also allows for the mounting of additional accessories.

## FEATURES

---

Description: For full height mounting of swing frames in steel

Material: 3 mm zinc plated steel.

Mounting requirements: Support bars (ESFB) 600 mm wide can also be mounted directly into a 1200 mm wide enclosure by means of a VBD. Support bars (ESFB) 800 mm wide can also be mounted directly in 1600 mm wide enclosures.

Pack quantity: One complete kit for a swing frame.

SPECIFICATIONS

- Thickness:** 3mm
- Material:** Mild Steel
- Finish:** Zinc Plated

| Table 1/1      |                |        |        |       |                    |            |
|----------------|----------------|--------|--------|-------|--------------------|------------|
| Catalog Number | Article Number | Height | Width  | Depth | Enclosure Material | Quick Ship |
| ESFB12         | ESFB12         | 1200mm | 1200mm | 103mm | Mild Steel         | No         |
| ESFB06         | ESFB06         | 600mm  | 600mm  | 103mm | Mild Steel         | No         |
| ESFB10         | ESFB10         | 1000mm | 1000mm | 103mm | Mild Steel         | No         |
| ESFB08         | ESFB08         | 800mm  | 800mm  | 103mm | Mild Steel         | No         |

ADDITIONAL PRODUCT DETAILS

To mount 2 x ESFC swing frames, an additional mounting kit ESFB12XKIT is required.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE