


# Solar Bonding Lug



## CERTIFICATIONS



## FEATURES

Bonds the frames and mounting structures of solar photo voltaic systems in accordance with NEC® requirements

Copper alloy is corrosion resistant and galvanically compatible with copper grounding conductors and aluminum photovoltaic module frames

Lay-in feature allows for easy positioning along multiple frames

## SPECIFICATIONS

**Material:** Bronze;Stainless Steel 18-8 (EN 1.4305)


**Finish:** Tinned

Table 1/1

Catalog Number	Direct Burial	Conductor Size	Hole Size (HS)	Screw Included	Thread Size (TS)
EL6CSNH	No	#14 Solid - #6 Stranded	5.61 mm	No	
EL6CSDB8	Yes	#14 Solid - #6 Stranded	5.61 mm	Yes	8" UNS

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ **WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**