

# Ventilated Top And Bottom Panels For Floor Standing Enclosures, DPCV



Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted. The ventilation panels also provide natural ventilation.

## FEATURES

Description: Required to cover the remaining space at the top and bottom. With ventilation slots for added heat dissipation in switchgear enclosures. Used in combination with horizontal dividers CDH/CDHK

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 20.

Mounting requirements: DPCV covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPCV is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: 2 panels with mounting accessories.

SPECIFICATIONS

**Thickness:** 1.75mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1						
Catalog Number	Height	Width	Depth	Height 1	Height 2	Enclosure Material
DPCV0714R5	104mm	400mm	17mm	70mm	100mm	Mild Steel
DPCV0716R5	104mm	600mm	17mm	70mm	100mm	Mild Steel
DPCV0718R5	104mm	800mm	17mm	70mm	100mm	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE