

# nVent CADDY Speed Link SLK with Hook



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Also available in Y-hook configuration

## SPECIFICATIONS

<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel; Polypropylene; Zinc Alloy
<b>Complies With:</b>	SMACNA HVAC-DCS

Table 1/3

Catalog Number	Article Number	E-Number	Wire Rope Diameter	Wire Rope Length	A	B
----------------	----------------	----------	--------------------	------------------	---	---

SLK15L3	196510	1342895	1.5 mm	3m	48 mm	18 mm
SLK15L5	196511	1342896	1.5 mm	5m	48 mm	18 mm
SLK15L2	196509	1342894	1.5 mm	2m	48 mm	18 mm
SLK15L2R2	196614	1319666	1.5 mm	2m	48 mm	18 mm
SLK15L3R2	196615	1319667	1.5 mm	3m	48 mm	18 mm
SLK15L10	196513	1342897	1.5 mm	10m	48 mm	18 mm
SLK15L1	196508	1342893	1.5 mm	1m	48 mm	18 mm
SLK2L10	196542	1342886	2 mm	10m	57 mm	22 mm
SLK2L2	196538	1342883	2 mm	2m	57 mm	22 mm
SLK2L5	196540	3435524	2 mm	5m	57 mm	22 mm
SLK2L1	196537	3435521	2 mm	1m	57 mm	22 mm
SLK2L3R2	196620	3435543	2 mm	3m	57 mm	22 mm
SLK2L3	196539	3435523	2 mm	3m	57 mm	22 mm
SLK2L2R2	196619	3435542	2 mm	2m	57 mm	22 mm
SLK3L10	196705	1305144	3 mm	10m	57.6 mm	23.2 mm
SLK3L2	196701	3435557	3 mm	2m	57.6 mm	23.2 mm
SLK3L3	196702	3435558	3 mm	3m	57.6 mm	23.2 mm
SLK3L5	196703	1305143	3 mm	5m	57.6 mm	23.2 mm
SLK3L3R2	196625	3435548	3 mm	3m	57.6 mm	23.2 mm

SLK3L5R2	196626	3435549	3 mm	5m	57.6 mm	23.2 mm
SLK3L1	196700	3435556	3 mm	1m	57.6 mm	23.2 mm

Table 2/3						
Catalog Number	Article Number	E-Number	C	Height (H)	Width (W)	Thickness (T)
SLK15L3	196510	1342895	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L5	196511	1342896	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L2	196509	1342894	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L2R2	196614	1319666	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L3R2	196615	1319667	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L10	196513	1342897	4.5 mm	55 mm	19 mm	12.5 mm
SLK15L1	196508	1342893	4.5 mm	55 mm	19 mm	12.5 mm
SLK2L10	196542	1342886	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L2	196538	1342883	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L5	196540	3435524	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L1	196537	3435521	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L3R2	196620	3435543	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L3	196539	3435523	5.5 mm	55 mm	19 mm	12.5 mm
SLK2L2R2	196619	3435542	5.5 mm	55 mm	19 mm	12.5 mm
SLK3L10	196705	1305144	6.1 mm	62 mm	24 mm	16 mm


CatalogNumber	Article Number	E-Number	C	Height (H)	Width (W)	Thickness (T)
SLK3L2	196701	3435557	6.1 mm	62 mm	24 mm	16 mm
SLK3L3	196702	3435558	6.1 mm	62 mm	24 mm	16 mm
SLK3L5	196703	1305143	6.1 mm	62 mm	24 mm	16 mm
SLK3L3R2	196625	3435548	6.1 mm	62 mm	24 mm	16 mm
SLK3L5R2	196626	3435549	6.1 mm	62 mm	24 mm	16 mm
SLK3L1	196700	3435556	6.1 mm	62 mm	24 mm	16 mm

Table 3/3

Catalog Number	Article Number	E-Number	Angle (a)	Static Load	Certifications
SLK15L3	196510	1342895	90 ° Max	195N	SMACNA, UL, cUL
SLK15L5	196511	1342896	90 ° Max	195N	UL, SMACNA, cUL
SLK15L2	196509	1342894	90 ° Max	195N	SMACNA, UL, cUL
SLK15L2R2	196614	1319666	90 ° Max	195N	UL, SMACNA, cUL
SLK15L3R2	196615	1319667	90 ° Max	195N	UL, cUL, SMACNA
SLK15L10	196513	1342897	90 ° Max	195N	UL, cUL, SMACNA
SLK15L1	196508	1342893	90 ° Max	195N	UL, SMACNA, cUL
SLK2L10	196542	1342886	90 ° Max	440N	SMACNA, UL, cUL
SLK2L2	196538	1342883	90 ° Max	440N	SMACNA, cUL, UL
SLK2L5	196540	3435524	90 ° Max	440N	UL, SMACNA, cUL
SLK2L1	196537	3435521	90 ° Max	440N	cUL, UL, SMACNA

Catalog Number	Article Number	E-Number	Angle (a)	Static Load	Certifications
SLK2L3R2	196620	3435543	90 ° Max	440N	UL, cUL, SMACNA
SLK2L3	196539	3435523	90 ° Max	440N	UL, cUL, SMACNA
SLK2L2R2	196619	3435542	90 ° Max	440N	cUL, UL, SMACNA
SLK3L10	196705	1305144	90 ° Max	890N	SMACNA
SLK3L2	196701	3435557	90 ° Max	890N	SMACNA
SLK3L3	196702	3435558	90 ° Max	890N	SMACNA
SLK3L5	196703	1305143	90 ° Max	890N	SMACNA
SLK3L3R2	196625	3435548	90 ° Max	890N	SMACNA
SLK3L5R2	196626	3435549	90 ° Max	890N	SMACNA
SLK3L1	196700	3435556	90 ° Max	890N	SMACNA

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

