

VIA-DU-20 Control Unit



This product is currently being phased out, to be replaced by the all-new Elexant 650c-Modbus. nVent RAYCHEM VIA-DU-20 is an energy efficient control unit for ramp heating, surface snow melting and de-icing applications. Equipped with ground temperature and moisture sensors, the system is only energised when these are both activated. An optional ambient temperature sensor is available, for identifying risk of freezing rain.

FEATURES

Simple and fast to install and operate

Energy saving: circuits energized only when ground temperature and moisture sensors are activated

BMS connection and alarm contacts for remote alarm function

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

Table 1/2									
Catalog Number	Item Name	IP Rating	Sensor Type	Pavement Moisture Sensor	Adjustment Range, Frost Protection	Power Consumption, Standby			
599514-000	VIA-DU-20	IP65	Remote Sensor	Yes	1 – 6 °C	5 W			

Table 2/2								
Catalog Number	Item Name	Height	Width	Depth				
599514-000	VIA-DU-20	54 mm	190 mm	58 mm				

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com