

2 Hole Lug, GL Style

Data Solutions



FEATURES

Provides an efficient bolting surface for grounding and power applications

Electrolytic grade copper

For use with nVent ERICO Cadweld type GL connections only

SPECIFICATIONS

Material: Copper

Finish: Tinned

Table 1/2

Catalog Number	Article Number	Type	Height (H)	Length (L)	Width (W)	Thickness (T)
B122CE	183660	NEMA®	11.18mm	81.03mm	25.4mm	3.18mm
B123CE03		Non-NEMA®	11.18mm	62.74mm	25.4mm	3.18mm
B122DE		NEMA®	11.18mm	82.55mm	25.4mm	4.76mm
B122DE002		NEMA®	11.18mm	62.74mm	25.4mm	4.76mm


CatalogNumber	Article Number	Type	Height (H)	Length (L)	Width (W)	Thickness (T)
B122EE		NEMA®	11.18mm	82.55mm	25.4mm	6.35mm
B122EG		NEMA®	11.18mm	82.55mm	38.1mm	6.35mm
B122EG002		Non-NEMA®	11.18mm	82.55mm	82.55mm	6.35mm
B123EG03		Non-NEMA®	11.18mm	82.55mm	38.1mm	6.35mm

Table 2/2						
Catalog Number	Article Number	A	B	Hole Size (HS)	Angle (a)	Equivalent Conductor Size
B122CE	183660	15.9mm	44.45mm	14.29mm	90°	80.63mm ²
B123CE03		15.9mm	44.45mm	11.11mm	90°	80.63mm ²
B122DE		15.9mm	44.45mm	14.29mm	90°	120.94mm ²
B122DE002		15.9mm	44.45mm	11.11mm	90°	120.94mm ²
B122EE		15.9mm	44.45mm	14.29mm	90°	161.26mm ²
B122EG		15.9mm	44.45mm	14.29mm	90°	241.89mm ²
B122EG002		15.9mm	44.45mm	17.46mm	45°	524.09mm ²
B123EG03		15.9mm	44.45mm	11.11mm	90°	241.89mm ²

ADDITIONAL PRODUCT DETAILS

For sizes not listed, contact us.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE