

# nVent LENTON Interlok Position Transition Grout-Fill Coupler



## FEATURES

Designed to splice different diameter bars

Positional feature allows the threaded coupler end to telescope out to close a gap between forms and to allow alignment of the grout tubes

Over-sized cavity allows for greater field tolerance

Taper-threaded end helps prevent movement of the reinforcing bars and eliminate misalignment

Requires less grout than most competitive systems

## SPECIFICATIONS

Table 1/3

| Catalog Number | Material  | Finish | Packaging | Rebar Size, Metric | Rebar Size, US | Diameter 1 (Ø1) |
|----------------|-----------|--------|-----------|--------------------|----------------|-----------------|
| LK1110STHD     | Cast Iron | Plain  | Standard  | 36 mm, 32 mm       | #11, #10       | 80 mm           |

Table 2/3

| Catalog Number | Diameter 2 (Ø2) | Length 1 (L1) | Length 2 (L2) | Length 3 (L3) | Bar Depth (BD) | Coupler Body (CB) |
|----------------|-----------------|---------------|---------------|---------------|----------------|-------------------|
| LK1110STHD     | 62 mm           | 384 mm        | 410 mm        | 251mm         | 40mm           | 305mm             |

Table 3/3

| Catalog Number | Unit Weight |
|----------------|-------------|
|----------------|-------------|

LK1110STHD

4.59 kg


**Designed to Meet:**

AASHTO;ABNT NBR 8548:1984;ACI 318 Type 1 (125% Specified Yield);ACI 318 Type 2 (Specified Tensile);ACI 349;ACI 359;AS3600

**ADDITIONAL PRODUCT DETAILS**

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

**DIAGRAMS****WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY****ERICO****HOFFMAN****ILSCO****SCHROFF****TRACHTE**