

Strike Pad, Metric Thread



FEATURES

316L Stainless Steel used in areas where a better aesthetic finish is preferred

Ideal for environments that are conducive to corrosive effects, such as coastal/high salinity


Provides an exposed attractive point on conductor systems hidden in the building's fabric, e.g. below the tiles of a pitched roof

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Diameter (Ø)	Thread Length (TL)	Height (H)	Thread Size (TS)	Unit Weight
SSP100	Stainless Steel 316L (EN 1.4404)	100 mm	10mm	25.5 mm	M6	0.36 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE