

# Rail Joint Bond, Power



The nVent ERICO Cadweld joint bonds are intended to be welded to the head of the rail profile within the confines of the joint bar. To ensure connection integrity, the attachment shall be made using nVent ERICO Cadweld welding material.

## FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable


## SPECIFICATIONS

**Finish:** Bare  
**Bond Terminal Style:** C  
**Material:** Copper

Table 1/1

Catalog Number	Article Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
CBX5	515060	95 mm <sup>2</sup> Stranded	180 mm	30 mm	14.28 mm
CBX5L	515100	95 mm <sup>2</sup> Stranded	405 mm	30 mm	14.28 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE