

PVT1 Replacement Module, 750 V Max Continuous Operating Voltage (Ucpv)

CATALOG NUMBER

PVT1750M



CERTIFICATIONS



FEATURES

Replacement module for PVT1 photovoltaic surge protection devices

PRODUCT ATTRIBUTES

Max Continuous Operating Voltage (Ucpv): 750V

Nominal Discharge Current (In), IEC: 20kA 8/20 μ s

Total Discharge Current (Itotal): 10;40

Voltage Protection Level (Up): 5000V

Response Time: 25 ns Max

Short Circuit Current Rating (Iscrr): 11kA

Max Continuous Operating Voltage (Vpdc): 750 VDC

Voltage Protection Rating (VPR): 4000V

Nominal Discharge Current (In), UL: 20kA 8/20 μ s

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE