

# DT2 DIN Rail Surge Protection Class II, 1+1 Mode



## CERTIFICATIONS



## FEATURES

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


## SPECIFICATIONS

Catalog Number	DT27511R	DT230011R
Nominal System Voltage (Un)	60 V	240 V
Max Continuous Operating Voltage (Uc)	305 V N-PE 75 V L-N	300 V L-N 305 V N-PE
Nominal Discharge Current (In), IEC, L-N	20kA 8/20 $\mu$ s	20kA 8/20 $\mu$ s
Nominal Discharge Current (In), IEC, N-PE	40kA 8/20 $\mu$ s	40kA 8/20 $\mu$ s

Catalog Number	DT27511R	DT230011R
Max Discharge Current (I <sub>max</sub> ), IEC, L-N	50kA 8/20 μs	50kA 8/20 μs
Max Discharge Current (I <sub>max</sub> ), IEC, N-PE	65kA 8/20 μs	65kA 8/20 μs
Voltage Protection Level (Up), L-N	800V	1500V
Voltage Protection Level (Up), N-PE	1500V	1500V
Back-Up Fuse @ I <sub>sc</sub>	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz	50 - 60 Hz
Response Time, L-N	25 ns Max	25 ns Max
Response Time, N-PE	100 ns Max	100 ns Max
Protection Modes	L-N N-PE	L-N N-PE
Short Circuit Current Rating (I <sub>sc</sub> )	25kA 50kA	25kA 50kA
Temporary Over Voltage 120 min (U <sub>t</sub> /mode), L-N	114 V Withstand	442 V Safe Fail
Temporary Over Voltage Withstand 200 ms (U <sub>t</sub> ), N-PE	1200V	1200V
Temporary Over Voltage Withstand 5 s (U <sub>t</sub> ), L-N	114V	337V
Nominal Discharge Current (I <sub>n</sub> ), UL	20kA 8/20 μs	20kA 8/20 μs
Short Circuit Current Rating (SCCR)	100kA	150kA
Voltage Protection Rating (VPR), L-N	330V	1200V
Voltage Protection Rating (VPR), N-PE	1000V	1000V
Technology	Thermal Disconnect	Thermal Disconnect
Connection, Solid	35 mm <sup>2</sup> Max	35 mm <sup>2</sup> Max
Connection, Stranded	25 mm <sup>2</sup> Max	25 mm <sup>2</sup> Max
Torque (TQ)	4.5 N·m	4.5 N·m
Humidity	5 - 95	5 - 95
Temperature	-35 to 85 °C	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC

Catalog Number	DT27511R	DT230011R
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Depth (D)	69mm	69mm
Height (H)	90 mm	90 mm
Width (W)	36 mm	36 mm
Unit Weight	0.23 kg	0.24 kg
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 2 IEC® 61643-11 Class II	EN 61643-11 Type 2 IEC® 61643-11 Class II
Replacement Module	DT275M SGT240M	DT2300M SGT240M

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**