

Front Panel, Flat, Refrofit Shielding, D-Sub Cutouts



Flat front panel with cutout for D-Sub connectors.
Shieldable for stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

For stainless steel EMC gasket

Al, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Rack Height:	3U
Rack Width:	4HP
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel

Type: Front Panel without Handle

EMC Shielding: No (Retrofittable)

Table 1/2

Catalog Number	Package Quantity	Mounting	EMC Gasket Type	Front Finish	Rear Finish	Number of Pins
30118-348	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(1) 9
30118-349	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(1) 15
30118-350	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(1) 25
30118-351	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(2) 9
30118-352	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(2) 15
30118-353	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(2) 25
30118-354	1	Screw-on Front	Stainless Steel	Anodized	Conductive	(3) 9

Table 2/2

Catalog Number	Treated Edges	Complies With	Depth (D)	Height (H)	Width (W)	Quick Ship
30118-348	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No
30118-349	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No
30118-350	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No
30118-351	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No
30118-352	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No
30118-353	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No

CatalogNumber	Treated Edges	Complies With	Depth (D)	Height (H)	Width (W)	Quick Ship
30118-354	No	IEC 60297-3-101, IEEE 1101.1/10	2.5mm	128.4mm	19.98mm	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order stainless steel EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS



