

# Complete Toolbox for PI Heaters, 4-25 mm<sup>2</sup>



nVent RAYCHEM PI-TOOL-SET-02 is a handy tool box containing all materials required to connect polymer insulated (PI) heating cables to a suitable cold lead and also to splice two PI heating cables (4-25 mm<sup>2</sup>). In addition to the crimp tool and dies, the kit contains a variety of crimps.

## FEATURES

Includes pneumatical crimp tool and appropriate dies to execute connections of 4 mm<sup>2</sup> and larger

Includes crimps types PI-CRP-07 to PI-CRP-24

## SPECIFICATIONS

Table 1/2

| Catalog Number | Item Name      | Material | Model    | Crimp Tool Type | Height | Width  |
|----------------|----------------|----------|----------|-----------------|--------|--------|
| 1244-000584    | PI-TOOL-SET-02 | Metal    | Tool Box | Hydraulic       | 325 mm | 380 mm |

Table 2/2

| Catalog Number | Item Name      | Depth |
|----------------|----------------|-------|
| 1244-000584    | PI-TOOL-SET-02 | 50 mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**