


# Telecom Grounding Busbar

## Data Solutions



### CERTIFICATIONS



### FEATURES

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

### SPECIFICATIONS

**Thickness (T):** 6.35mm

**Width (W):** 50.8mm

**Material:** Copper

Table 1/2


Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
----------------	-------------	---------------	---------------	-------------------	-----------------------------	-------------------

TGBA29L18PT	Yes	737mm	457mm	8mm	18	11mm
TGBA12L06PT	Yes	305mm	229mm	8mm	6	11mm
TGBA12L06P	No	305mm	229mm	8mm	6	11mm
TGBA20L12PT	Yes	508mm	229mm	8mm	12	11mm
TGBA24L14P	No	610mm	457mm	8mm	14	11mm
TGBA24L14PT	Yes	610mm	457mm	8mm	14	11mm

Table 2/2

Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA29L18PT	5	25.4mm	28.6mm	15.9mm
TGBA12L06PT	3	25.4mm	28.6mm	15.9mm
TGBA12L06P	3	25.4mm	28.6mm	15.9mm
TGBA20L12PT	3	25.4mm	28.6mm	15.9mm
TGBA24L14P	5	25.4mm	28.6mm	15.9mm
TGBA24L14PT	5	25.4mm	28.6mm	15.9mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**