

# MFWC Manual nVent ERIFLEX Flexibar Work Center



## CERTIFICATIONS



## FEATURES

Modular table with large work surface and storage for manual nVent ERIFLEX Flexibar tools

Tools can be fixed directly to interchangeable tiles allowing tools to be quickly moved from one level to another

Non-slip bakelite coated plywood tiles fix into place with included wing knobs

Includes nVent ERIFLEX Flexibar Small Bending and Folding Tool

Forklift rail, locking directional wheels and built-in handles provide easy mobility

Built-in handle is extendable to accommodate long pieces of nVent ERIFLEX Flexibar

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material       | Height (H) | Length         | Width (W) | A      |
|----------------|----------------|----------------|------------|----------------|-----------|--------|
| MFWC           | 558940         | Steel, Plywood | 928 mm     | 1200 - 1913 mm | 700 mm    | 348 mm |

Table 2/2

| Catalog Number | Article Number | Static Load | Unit Weight |
|----------------|----------------|-------------|-------------|
| MFWC           | 558940         | 400N        | 95 kg       |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**