

IceStop Self-Regulating Heating Cable



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

SPECIFICATIONS

Nominal Thickness:	6 mm
Nominal Width:	14 mm
Nominal Cable Weight:	130 g/m
Supply Voltage:	208 – 240 V
Min Installation Temperature:	-18 °C
Color:	Black
Ground Path Type:	Braid
Conductor Material:	Nickel-Plated Copper

Table 1/1

Catalog Number	Item Name	Nominal Power Output, In Air @ 0°C, 230V	Nominal Power Output, In Ice Water @ 0°C, 230V	Outer Jacket Material
092961-000	GM-2XT	18 W/m	36 W/m	Fluoropolymer

Catalog Number	Item Name	Nominal PowerOutput, In Air @ 0°C,230V	Nominal PowerOutput, In Ice Water @0°C, 230V	Outer Jacket Material
446105-000	GM-2X	18 W/m	36 W/m	Modified Polyolefin

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

**Europe, Middle East,
Africa**
Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific
Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America
Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT