


Front Panel, U-profile, Retrofit Shielding



U-profile front panel for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

Depth (D):	2.5mm
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
----------------	-------------	------------	------------------	----------	--------------	-------------

30849-001	3U	2HP	1	Screw-on Front	Anodized	Conductive
30849-004	3U	3HP	1	Screw-on Front	Anodized	Conductive
30849-002	6U	2HP	1	Screw-on Front	Anodized	Conductive
30848-354	3U	4HP	1	Screw-on Front	Anodized	Conductive
30848-380	3U	6HP	1	Screw-on Front	Anodized	Conductive
30849-005	6U	3HP	1	Screw-on Front	Anodized	Conductive
30848-382	3U	7HP	1	Screw-on Front	Anodized	Conductive
30848-356	3U	8HP	1	Screw-on Front	Anodized	Conductive
30848-355	6U	4HP	1	Screw-on Front	Anodized	Conductive
30848-357	6U	8HP	1	Screw-on Front	Anodized	Conductive
30848-384	3U	9HP	1	Screw-on Front	Anodized	Conductive
30848-386	3U	10HP	1	Screw-on Front	Anodized	Conductive
30848-358	3U	12HP	1	Screw-on Front	Anodized	Conductive
30848-381	6U	6HP	1	Screw-on Front	Anodized	Conductive
20848-013	3U	14HP	1	Screw-on Front	Anodized	Conductive
30848-383	6U	7HP	1	Screw-on Front	Anodized	Conductive
20848-015	3U	16HP	1	Screw-on Front	Anodized	Conductive
20848-108	6U	16HP	1	Screw-on Front	Anodized	Conductive
20848-206	2U	28HP	1	Screw-on Front	Anodized	Conductive

20848-020	3U	21HP	1	Screw-on Front	Anodized	Conductive
30848-387	6U	10HP	1	Screw-on Front	Anodized	Conductive
30848-359	6U	12HP	1	Screw-on Front	Anodized	Conductive
20848-260	2U	42HP	1	Screw-on Front	Anodized	Conductive
20848-027	3U	28HP	1	Screw-on Front	Anodized	Conductive
20848-106	6U	14HP	1	Screw-on Front	Anodized	Conductive
20848-268	4U	28HP	1	Screw-on Front	Anodized	Conductive
20848-047	3U	42HP	1	Screw-on Front	Anodized	Conductive
20848-113	6U	21HP	1	Screw-on Front	Anodized	Conductive
20848-261	2U	63HP	1	Screw-on Front	Anodized	Conductive
20848-269	4U	42HP	1	Screw-on Front	Anodized	Conductive
20848-120	6U	28HP	1	Screw-on Front	Anodized	Conductive
20848-262	2U	84HP	1	Screw-on Front	Anodized	Conductive
20848-647	5U	28HP	1	Screw-on Front	Anodized	Conductive
20848-648	5U	42HP	1	Screw-on Front	Anodized	Conductive
20848-068	3U	63HP	1	Screw-on Front	Anodized	Conductive
20848-270	4U	42HP	1	Screw-on Front	Anodized	Conductive
20848-097	3U	84HP	1	Screw-on Front	Anodized	Conductive
20848-139	6U	42HP	1	Screw-on Front	Anodized	Conductive

20848-649	5U	63HP	1	Screw-on Front	Anodized	Conductive
20848-271	4U	84HP	1	Screw-on Front	Anodized	Conductive
20848-160	6U	63HP	1	Screw-on Front	Anodized	Conductive
20848-650	5U	84HP	1	Screw-on Front	Anodized	Conductive
20848-189	6U	84HP	1	Screw-on Front	Anodized	Conductive
30848-385	3U	9HP	1	Screw-on Front	Anodized	Conductive
20848-280	9U	84HP	1	Screw-on Front	Anodized	Conductive
30848-378	3U	5HP	1	Screw-on Front	Anodized	Conductive
30848-379	6U	5HP	1	Screw-on Front	Anodized	Conductive

Table 2/2

Catalog Number	Treated Edges	Complies With	Height (H)	Width (W)	Certifications	Quick Ship
30849-001	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	9.8mm	RoHS	No
30849-004	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	14.9mm	RoHS	No
30849-002	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	9.8mm	RoHS	No
30848-354	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	RoHS	No
30848-380	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	30.1mm	RoHS	No
30849-005	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	14.9mm		No

CatalogNumber	Treated Edges	Complies With	Height (H)	Width (W)	Certifications	Quick Ship
30848-382	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	35.2mm	RoHS	No
30848-356	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	40.3mm	RoHS	No
30848-355	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	20mm	RoHS	No
30848-357	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	40.3mm	RoHS	No
30848-384	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	45.38mm		No
30848-386	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	50.5mm	RoHS	No
30848-358	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	60.6mm	RoHS	No
30848-381	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	30.1mm	RoHS	No
20848-013	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	70.8mm	RoHS	No
30848-383	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	35.2mm	RoHS	No
20848-015	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	80.9mm	RoHS	No
20848-108	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	80.9mm	RoHS	No
20848-206	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	141.9mm		No
20848-020	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	106.3mm	RoHS	No
30848-387	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	50.5mm	RoHS	No

CatalogNumber	Treated Edges	Complies With	Height (H)	Width (W)	Certifications	Quick Ship
30848-359	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	60.6mm	RoHS	No
20848-260	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	213mm		No
20848-027	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	141.9mm	RoHS	No
20848-106	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	70.8mm	RoHS	No
20848-268	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	141.9mm	RoHS	No
20848-047	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	213mm	RoHS	No
20848-113	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	106.3mm	RoHS	No
20848-261	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	319.7mm		No
20848-269	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS	No
20848-120	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	141.9mm	RoHS	No
20848-262	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	426.4mm	RoHS	No
20848-647	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	141.9mm		No
20848-648	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	213mm		No
20848-068	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	319.7mm	RoHS	No
20848-270	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS	No

CatalogNumber	Treated Edges	Complies With	Height (H)	Width (W)	Certifications	Quick Ship
20848-097	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	426.4mm	RoHS	No
20848-139	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	213mm	RoHS	No
20848-649	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	319.7mm		No
20848-271	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	426.4mm	RoHS	No
20848-160	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	319.7mm	RoHS	No
20848-650	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	426.4mm		No
20848-189	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	426.4mm	RoHS	No
30848-385	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	45.38mm		No
20848-280	No	IEC 60297-3-101, IEEE 1101.1/10	395.1mm	426.4mm	RoHS	No
30848-378	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	25mm	RoHS	No
30848-379	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	25mm	RoHS	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).


Differences in finish between 2 ... 12 HP and 14 ... 84 HP.

2 ... 12 HP: one-part U-profile

Please order textile EMC gasket separately.

Standard pack quantity: 2 to 28HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE