

# nVent ERICO Quickfill No-Mix Ground Enhancing Backfill

# **Power Utilities**



nVent ERICO Quickfill is a no-mix ground-enhancing backfill that reduces resistance to ground and enables convenient installations. Quickfill is designed to minimize dust and eliminate mixing. It is the ideal material to use in areas of poor conductivity such as rocky ground, mountain tops, and sandy soil. Once installed, Quickfill is maintenance-free, not requiring periodic charging. Dry ground enhancement materials are more sensitive to seasonal variability than cement-based materials.

### **FEATURES**

Lowers system resistance to ground

Low-dust formulation

Water not needed to install or perform

Fast installation with no mixing or cure time required

Can be installed in below-freezing temperatures

Does not dissolve, decompose, or leach out with time

Corrosion-resistant

Sulfur content below 2% per IEC 62561-7

Easy-to-handle 25 lb (11.3 kg) bags

Requires only one person to install

Resistance measurements can be taken immediately after installation

Complies to the U.S. Environmental Protection Agency (EPA) Toxicity Characteristic Leaching Procedure (TCLP), EPA test method 1311

Complies to EN 12457-2 Characterization of Waste Leaching Procedure, ENV 12506 and ENV 13370

### **SPECIFICATIONS**

Table 1/1				
Catalog Number	Unit Weight			
QF25	11.300 kg			

Specifications				
Parameter	Values	Test Method		
Resistivity	< 15 $\Omega$ -cm when mixed with 40% water by weight < 25 $\Omega$ -cm when tested dry	4-Electrode method per ASTM G57-06		
Sulfur Content	< 2%	ISO 4689-3		
Leaching	< reporting limit for all substances	EN 12457-2 TCLP per EPA 1311		
Density	993 kg/m3	-		

Estimated Trench Length per Bag of Quickfill					
Trench Width	Total Thickness of Quickfill				
Trendi Widii	10 cm	13 cm	15 cm		
10 cm	1.10 m	0.88 m	0.73 m		
15 cm	0.73 m	0.58 m	0.49 m		
20 cm	0.55 m	0.43 m	0.37 m		
25 cm	0.43 m	0.34 m	0.27 m		
30 cm	0.37 m	0.27 m	0.24 m		

Estimated Bags of Quickfill for Backfilling Around Ground Rods						
Diameter	Depth					
Diameter	1.5 m	1.8 m	2.4 m	3.0 m	4.6 m	6.1 m
10 cm	1.1	1.3	1.8	2.2	3.3	4.4
15 cm	2.5	3.0	3.9	4.9	7.4	9.8
20 cm	4.4	5.2	7.0	8.7	13.0	17.4
25 cm	6.8	8.2	10.9	13.6	20.3	27.1
30 cm	9.8	11.7	15.6	19.5	29.3	39.0

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY **ERICO HOFFMAN TRACHTE SCHROFF ILSCO**