


nVent ERICO Cadweld Exolon, Cable to Ground Rod or Other Rounds



Developed in 1988, nVent ERICO Cadweld Exolon connections represented a significant advancement in welded electrical connections for sensitive indoor applications like data centers, hospitals, and other clean room environments. The virtual elimination of smoke and a unique electronic starting system makes this an ideal solution for sensitive applications. Each nVent ERICO Cadweld Exolon package contains ceramic filters that produce an extremely low emission connection.

CERTIFICATIONS



DIAGRAMS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

SPECIFICATIONS

Table 1/2

| Catalog Number | Mold Family | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size | Conductor Outer Diameter, Nominal |
|----------------|-------------|-----------------|------------------------------|-----------------------------|----------------|-----------------------------------|
| XLGRC181L | GR | Copper-bonded | 3/4" | 17.32 mm | #4 Concentric | 5.89mm |
| XLGTC161T | GT | Copper-bonded | 5/8" | 14.3 mm | #2 Solid | 6.53mm |
| XLGTC181T | GT | Copper-bonded | 3/4" | 17.32 mm | #2 Solid | 6.53mm |
| XLGTC161V | GT | Copper-bonded | 5/8" | 14.3 mm | #2 Concentric | 7.42mm |
| XLGTC181V | GT | Copper-bonded | 3/4" | 17.32 mm | #2 Concentric | 7.42mm |
| XLGRC182C | GR | Copper-bonded | 3/4" | 17.32 mm | 1/0 Concentric | 9.47mm |
| XLGTC182C | GT | Copper-bonded | 3/4" | 17.32 mm | 1/0 Concentric | 9.47mm |
| XLGRC182G | GR | Copper-bonded | 3/4" | 17.32 mm | 2/0 Concentric | 10.62mm |
| XLGTC162G | GT | Copper-bonded | 5/8" | 14.3 mm | 2/0 Concentric | 10.62mm |
| XLGTC162GW | GT | Copper-bonded | 5/8" | 14.3 mm | 2/0 Concentric | 10.62mm |
| XLGTC182G | GT | Copper-bonded | 3/4" | 17.32 mm | 2/0 Concentric | 10.62mm |
| XLGTC332G | GT | Steel | 3/4" | 19.05 mm | 2/0 Concentric | 10.62mm |
| XLGRC182L | GR | Copper-bonded | 3/4" | 17.32 mm | 3/0 Concentric | 11.94mm |
| XLGTC182L | GT | Copper-bonded | 3/4" | 17.32 mm | 3/0 Concentric | 11.94mm |
| XLGYE182L | GY | Copper-bonded | 3/4" | 17.32 mm | 3/0 Concentric | 11.94mm |
| XLGRC162Q | GR | Copper-bonded | 5/8" | 14.3 mm | 4/0 Concentric | 13.41mm |
| XLGRC182Q | GR | Copper-bonded | 3/4" | 17.32 mm | 4/0 Concentric | 13.41mm |

| CatalogNumber | Mold Family | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size | Conductor OuterDiameter, Nominal |
|---------------|-------------|-----------------|------------------------------|-----------------------------|----------------------|----------------------------------|
| XLGTC162Q | GT | Copper-bonded | 5/8" | 14.3 mm | 4/0 Concentric | 13.41mm |
| XLGTC182Q | GT | Copper-bonded | 3/4" | 17.32 mm | 4/0 Concentric | 13.41mm |
| XLGTC182QW | GT | Copper-bonded | 3/4" | 17.32 mm | 4/0 Concentric | 13.41mm |
| XLGYE182Q | GY | Copper-bonded | 3/4" | 17.32 mm | 4/0 Concentric | 13.41mm |
| XLGTC189FW | GT | Copper-bonded | 3/4" | 17.32 mm | 19/#9 Copperweld | 14.53mm |
| XLGTC313Q | GT | Steel | 5/8" | 15.88 mm | 500 kcmil Concentric | 20.65mm |
| XLGRC183Q | GR | Copper-bonded | 3/4" | 17.32 mm | 500 kcmil Concentric | 20.65mm |

Table 2/2

| Catalog Number | Certifications |
|----------------|----------------|
| XLGRC181L | cUL, UL |
| XLGTC161T | UL, cUL |
| XLGTC181T | UL, cUL |
| XLGTC161V | cUL, UL |
| XLGTC181V | UL, cUL |
| XLGRC182C | cUL, UL |
| XLGTC182C | cUL, UL |
| XLGRC182G | UL, cUL |
| XLGTC162G | UL, cUL |

| Catalog Number | Certifications |
|----------------|----------------|
| XLGTC162GW | UL, cUL |
| XLGTC182G | UL, cUL |
| XLGTC332G | UL, cUL |
| XLGRC182L | cUL, UL |
| XLGTC182L | UL, cUL |
| XLGYE182L | cUL, UL |
| XLGRC162Q | UL, cUL |
| XLGRC182Q | cUL, UL |
| XLGTC162Q | cUL, UL |
| XLGTC182Q | cUL, UL |
| XLGTC182QW | UL, cUL |
| XLGYE182Q | UL, cUL |
| XLGTC189FW | |
| XLGTC313Q | |
| XLGRC183Q | |

| XL-XX-X-XX-XX-L-M-W | | |
|---------------------|----------------------------------|---|
| XL | ERICO CADWELD EXOLON Designation | |
| XX | Mold Family | |
| X | Price Key | |
| XX | Ground Rod Code | |
| XX | Conductor Code | |
| L* | Split Crucible | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M* | Mold Only | |
| W* | Wear Plates | Reduce mechanical abrasion of molds at cable entry points |

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE