

# nVent CADDY Cat 425 Adjustable Cable Support with BC200 Beam Clamp



#### **CERTIFICATIONS**





## **FEATURES**

Easy installation to beam flanges

Rotates 360 degrees to support various directional runs of cable

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray

cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems


Suitable for air handling spaces (plenum)

#### **SPECIFICATIONS**

Table 1/2									
Catalog Number	Article Number	Material	Finish	Diameter (Ø)	Area	Cable Capacity, Cat 5e			
CAT425BC200	181460	Steel, Polyethylene	Electrogalvaniz ed	100 mm, 150 mm	13181mm²	425			

Table 2/2									
Catalog Number	Article Number	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Flange Thickness (FT)	Torque (TQ)	Static Load			
CAT425BC200	181460	325	210	3.2 - 12.7 mm	3 N·m	450N			

## **DIAGRAMS**



### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

**TRACHTE** 

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN

ILSCO SCHROFF



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.