


Front Panel, U-profile, Retrofit Shielding

U-profile front panel for textile EMC gasket.



CERTIFICATIONS



FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

Depth (D):	2.5mm
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	EMC Gasket Type	Front Finish
----------------	-------------	------------	------------------	----------	-----------------	--------------

30849-001	3U	2HP	1	Screw-on Front	Textile	Anodized
30849-004	3U	3HP	1	Screw-on Front	Textile	Anodized
30849-002	6U	2HP	1	Screw-on Front	Textile	Anodized
30848-354	3U	4HP	1	Screw-on Front	Textile	Anodized
30848-380	3U	6HP	1	Screw-on Front	Textile	Anodized
30849-005	6U	3HP	1	Screw-on Front	Textile	Anodized
30848-382	3U	7HP	1	Screw-on Front	Textile	Anodized
30848-356	3U	8HP	1	Screw-on Front	Textile	Anodized
30848-355	6U	4HP	1	Screw-on Front	Textile	Anodized
30848-357	6U	8HP	1	Screw-on Front	Textile	Anodized
30848-384	3U	9HP	1	Screw-on Front	Textile	Anodized
30848-386	3U	10HP	1	Screw-on Front	Textile	Anodized
30848-358	3U	12HP	1	Screw-on Front	Textile	Anodized
30848-381	6U	6HP	1	Screw-on Front	Textile	Anodized
20848-013	3U	14HP	1	Screw-on Front	Textile	Anodized
30848-383	6U	7HP	1	Screw-on Front	Textile	Anodized
20848-015	3U	16HP	1	Screw-on Front	Textile	Anodized
20848-108	6U	16HP	1	Screw-on Front	Textile	Anodized
20848-206	2U	28HP	1	Screw-on Front	Textile	Anodized

20848-020	3U	21HP	1	Screw-on Front	Textile	Anodized
30848-387	6U	10HP	1	Screw-on Front	Textile	Anodized
30848-359	6U	12HP	1	Screw-on Front	Textile	Anodized
20848-260	2U	42HP	1	Screw-on Front	Textile	Anodized
20848-027	3U	28HP	1	Screw-on Front	Textile	Anodized
20848-106	6U	14HP	1	Screw-on Front	Textile	Anodized
20848-268	4U	28HP	1	Screw-on Front	Textile	Anodized
20848-047	3U	42HP	1	Screw-on Front	Textile	Anodized
20848-113	6U	21HP	1	Screw-on Front	Textile	Anodized
20848-261	2U	63HP	1	Screw-on Front	Textile	Anodized
20848-269	4U	42HP	1	Screw-on Front	Textile	Anodized
20848-120	6U	28HP	1	Screw-on Front	Textile	Anodized
20848-262	2U	84HP	1	Screw-on Front	Textile	Anodized
20848-647	5U	28HP	1	Screw-on Front	Textile	Anodized
20848-648	5U	42HP	1	Screw-on Front	Textile	Anodized
20848-068	3U	63HP	1	Screw-on Front	Textile	Anodized
20848-270	4U	42HP	1	Screw-on Front	Textile	Anodized
20848-097	3U	84HP	1	Screw-on Front	Textile	Anodized
20848-139	6U	42HP	1	Screw-on Front	Textile	Anodized

20848-649	5U	63HP	1	Screw-on Front	Textile	Anodized
20848-271	4U	84HP	1	Screw-on Front	Textile	Anodized
20848-160	6U	63HP	1	Screw-on Front	Textile	Anodized
20848-650	5U	84HP	1	Screw-on Front	Textile	Anodized
20848-189	6U	84HP	1	Screw-on Front	Textile	Anodized
30848-385	3U	9HP	1	Screw-on Front	Textile	Anodized
20848-280	9U	84HP	1	Screw-on Front	Textile	Anodized
30848-378	3U	5HP	1	Screw-on Front	Textile	Anodized
30848-379	6U	5HP	1	Screw-on Front	Textile	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	Height (H)	Width (W)	Certifications
30849-001	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	9.8mm	RoHS
30849-004	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	14.9mm	RoHS
30849-002	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	9.8mm	RoHS
30848-354	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	RoHS
30848-380	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	30.1mm	RoHS
30849-005	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	14.9mm	

CatalogNumber	Rear Finish	Treated Edges	Complies With	Height (H)	Width (W)	Certifications
30848-382	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	35.2mm	RoHS
30848-356	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	40.3mm	RoHS
30848-355	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	20mm	RoHS
30848-357	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	40.3mm	RoHS
30848-384	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	45.38mm	
30848-386	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	50.5mm	RoHS
30848-358	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	60.6mm	RoHS
30848-381	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	30.1mm	RoHS
20848-013	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	70.8mm	RoHS
30848-383	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	35.2mm	RoHS
20848-015	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	80.9mm	RoHS
20848-108	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	80.9mm	RoHS
20848-206	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	141.9mm	
20848-020	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	106.3mm	RoHS
30848-387	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	50.5mm	RoHS

CatalogNumber	Rear Finish	Treated Edges	Complies With	Height (H)	Width (W)	Certifications
30848-359	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	60.6mm	RoHS
20848-260	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	213mm	
20848-027	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	141.9mm	RoHS
20848-106	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	70.8mm	RoHS
20848-268	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	141.9mm	RoHS
20848-047	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	213mm	RoHS
20848-113	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	106.3mm	RoHS
20848-261	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	319.7mm	
20848-269	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS
20848-120	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	141.9mm	RoHS
20848-262	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	84mm	426.4mm	RoHS
20848-647	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	141.9mm	
20848-648	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	213mm	
20848-068	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	319.7mm	RoHS
20848-270	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS

CatalogNumber	Rear Finish	Treated Edges	Complies With	Height (H)	Width (W)	Certifications
20848-097	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	426.4mm	RoHS
20848-139	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	213mm	RoHS
20848-649	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	319.7mm	
20848-271	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	426.4mm	RoHS
20848-160	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	319.7mm	RoHS
20848-650	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	426.4mm	
20848-189	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	426.4mm	RoHS
30848-385	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	45.38mm	
20848-280	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	395.1mm	426.4mm	RoHS
30848-378	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	25mm	RoHS
30848-379	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	25mm	RoHS

Table 3/3

Catalog Number	Quick Ship
30849-001	No
30849-004	No
30849-002	No

Catalog Number	Quick Ship
30848-354	No
30848-380	No
30849-005	No
30848-382	No
30848-356	No
30848-355	No
30848-357	No
30848-384	No
30848-386	No
30848-358	No
30848-381	No
20848-013	No
30848-383	No
20848-015	No
20848-108	No
20848-206	No
20848-020	No
30848-387	No

Catalog Number	Quick Ship
30848-359	No
20848-260	No
20848-027	No
20848-106	No
20848-268	No
20848-047	No
20848-113	No
20848-261	No
20848-269	No
20848-120	No
20848-262	No
20848-647	No
20848-648	No
20848-068	No
20848-270	No
20848-097	No
20848-139	No
20848-649	No

Catalog Number	Quick Ship
20848-271	No
20848-160	No
20848-650	No
20848-189	No
30848-385	No
20848-280	No
30848-378	No
30848-379	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).

Differences in finish between 2 ... 12 HP and 14 ... 84 HP.

2 ... 12 HP: one-part U-profile

Please order textile EMC gasket separately.

Standard pack quantity: 2 to 28HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only.

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE