

Universal Sway Brace



The nVent CADDY Universal Sway Brace is an innovative, versatile solution providing seismic bracing for suspended pipes. Featuring a unique slotted hole pattern for easy slip-on installation, installers can eliminate the risk and inconvenience of loose hardware, making it an ideal choice for ensuring safety and compliance on the job.

CERTIFICATIONS



FEATURES

Used for both lateral and longitudinal sway brace applications

Snap-off bolt head helps enable easy installation and inspection

Works with 1" to 2" (25,4mm to 50,8mm) brace pipes to reduce inventory

Works with 12 gauge or thicker Type A solid strut as brace member

Meets NFPA®-13 and CEN/TS 1755:2021 requirements for seismic sway bracing

FM Approved with the following brace members: Type A Solid Strut (12 gauge or thicker) and 1-2 in Sch40/EN 10255H Pipe

FM Specification Tested with the following brace members: Type A Solid Strut (12 gauge or thicker) and 1-2 in Sch40/EN 10255H Pipe

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Pipe Size, Nominal	Cast Iron	NB/DN	Brace NB/DN	Width (W)
----------------	----------------	--------------------	-----------	-------	-------------	-----------

CSB0100	404516	25.4 mm		25	25 - 50 mm	38 mm
CSB0125	404517	31.75 mm		32	25 - 50 mm	38 mm
CSB0400	404522	101.6 mm	101.6mm	100	25 - 50 mm	38 mm
CSB0150	404518	38.1 mm	38.1mm	40	25 - 50 mm	38 mm
CSB0200	404519	50.8 mm	50.8mm	50	25 - 50 mm	38 mm
CSB0250	404520	63.5 mm	63.5mm	65	25 - 50 mm	38 mm
CSB0300	404521	76.2 mm	76.2mm	80	25 - 50 mm	38 mm
CSB0500	404523			125	25 - 50 mm	38 mm
CSB1000	404526	254 mm	254mm	250	25 - 50 mm	38 mm
CSB1200	404551	304.8 mm	304.8mm	300	25 - 50 mm	38 mm
CSB0600	404524	152.4 mm		150	25 - 50 mm	38 mm
CSB0800	404525	203.2 mm	203.2mm	200	25 - 50 mm	38 mm

Table 2/2

Catalog Number	Article Number	A	B	C	D	Certifications
CSB0100	404516	91 mm	33 mm	16 mm	126 mm	OSHDP, UL, FM Approved, Seismic, cUL
CSB0125	404517	91 mm	33 mm	18 mm	140 mm	UL, FM Approved, Seismic, OSHDP/HCAI, cUL
CSB0400	404522	91 mm	33 mm	26 mm	216 mm	UL, FM Approved, Seismic, OSHDP/HCAI, cUL

CatalogNumber	Article Number	A	B	C	D	Certifications
CSB0150	404518	91 mm	33 mm	19 mm	136 mm	UL, FM Approved, Seismic, OSHPD/HCAI, cUL
CSB0200	404519	91 mm	33 mm	21 mm	151 mm	UL, FM Approved, Seismic, OSHPD/HCAI, cUL
CSB0250	404520	91 mm	33 mm	24 mm	171 mm	UL, FM Approved, Seismic, OSHPD/HCAI, cUL
CSB0300	404521	91 mm	33 mm	25 mm	187 mm	UL, FM Approved, Seismic, OSHPD/HCAI, cUL
CSB0500	404523	91 mm	33 mm	25 mm	255 mm	UL, FM Approved, Seismic, OSHPD/HCAI, cUL
CSB1000	404526	91 mm	33 mm	25 mm	386 mm	UL, FM Approved, Seismic, OSHPD, cUL
CSB1200	404551	91 mm	33 mm	25 mm	429 mm	FM Approved, Seismic, OSHPD/HCAI
CSB0600	404524	91 mm	33 mm	29 mm	275 mm	UL, FM Approved, Seismic, cUL, OSHPD
CSB0800	404525	91 mm	33 mm	31 mm	331 mm	UL, FM Approved, Seismic, OSHPD, cUL

ADDITIONAL PRODUCT DETAILS

FM® Specification Tested for 1-1/2 in to 4 in pipe sizes using no hub cast iron pipe.

Load ratings for Sch 10 may also be applied to AS 1074 Medium, GB/T 3091, EN 10255 (Medium or Heavy), and JIS G3452 pipe.

Load ratings for Sch 40 may also be applied to AS 1074 Heavy, GB/T 3091, EN 10255 (Heavy), and JIS G3454 pipe.


Load ratings for FM approved lightwall may also be applied to AS 1074 Lightwall, EN 10255 L, EN 10220, and GB/T 8163 pipe.

FM Approved with 12 gauge or thicker Type A solid strut as brace member

UL Loads								
Part Number	Lateral				Longitudinal			
	Sch 10/Sch 40 Service Pipe	Bull Moose Eddy Flow Service Pipe	Wheatland Mega-Flow Service Pipe	Youngstown Fire-Flo Service Pipe	Sch 10/Sch 40 Service Pipe	Bull Moose Eddy Flow Service Pipe	Wheatland Mega-Flow Service Pipe	Youngstown Fire-Flo Service Pipe
CSB0100xxx	8006 N	N/A	N/A	N/A	4448 N	N/A	N/A	N/A
CSB0125xxx	8006 N	8006 N	8006 N	N/A	3025 N	3025 N	3025 N	N/A
CSB0150xxx	8006 N	8006 N	8006 N	8006 N	4448 N	4448 N	4448 N	4448 N
CSB0200xxx	8006 N	8006 N	8006 N	8006 N	5782 N	5782 N	5782 N	5782 N
CSB0250xxx	8006 N	8006 N	8006 N	8006 N	5782 N	5782 N	5782 N	5782 N
CSB0300xxx	8006 N	8006 N	8006 N	8006 N	6227 N	6227 N	6227 N	6227 N
CSB0400xxx	8006 N	8006 N	8006 N	8006 N	7561 N	7561 N	7561 N	7561 N
CSB0500xxx	8006 N	N/A	N/A	N/A	7561 N	N/A	N/A	N/A
CSB0600xxx	8006 N	N/A	8006 N	N/A	7561 N	N/A	7561 N	N/A
CSB0800xxx	8006 N	N/A	N/A	N/A	7561 N	N/A	N/A	N/A
CSB1000xxx	8451 N	N/A	N/A	N/A	8451 N	N/A	N/A	N/A
CSB1200xxx	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A

FM Loads								
Part Number	Horizontal Capacity per Installation Angle from Vertical							
	Lateral				Longitudinal			
	30° - 44°	45° - 59°	60° - 74°	75° - 90°	30° - 44°	45° - 59°	60° - 74°	75° - 90°
FM Approved Lightwall, Sch 10 and Sch 40 Service Pipes								
CSB0100xxx	6620 N	9380 N	11470 N	12890 N	5730 N	5510 N	5600 N	6220 N
CSB0125xxx	6130 N	8710 N	10670 N	11960 N	5730 N	5510 N	5600 N	6220 N
CSB0150xxx	6130 N	8710 N	10670 N	11960 N	5330 N	8270 N	9690 N	10000 N
CSB0200xxx	6130 N	8710 N	10670 N	11960 N	5330 N	8090 N	9690 N	10000 N
CSB0250xxx	6400 N	9020 N	11070 N	12410 N	5870 N	8090 N	9740 N	11120 N
CSB0300xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0400xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0500xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0600xxx	6490 N	9160 N	11200 N	12580 N	6270 N	8670 N	10450 N	11920 N
0.188" Wall and Sch 40 Service Pipes								
CSB0800xxx	5910 N	8360 N	10230 N	11470 N	6220 N	8540 N	10450 N	11740 N
CSB1000xxx	5910 N	8360 N	10230 N	11470 N	6220 N	8540 N	10450 N	11740 N
CSB1200xxx	7470 N	10540 N	12940 N	14500 N	7110 N	8270 N	9960 N	11520 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte

