

Air Terminal, Imperial Thread



CERTIFICATIONS



FEATURES

Lightning strike termination points for use with air terminal bases

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPA221	Aluminum		12.7 mm	Sharp	254 mm	1/2" UNC
LPA221ST	Aluminum		12.7 mm	Blunt	254 mm	1/2" UNC
LPA222	Aluminum		12.7 mm	Sharp	304.8 mm	1/2" UNC
LPA222ST	Aluminum		12.7 mm	Blunt	304.8 mm	1/2" UNC
LPA223	Aluminum		12.7 mm	Sharp	381 mm	1/2" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPA223ST	Aluminum		12.7 mm	Blunt	381 mm	1/2" UNC
LPA241	Aluminum		15.88 mm	Sharp	254 mm	5/8" UNC
LPA241ST	Aluminum		15.88 mm	Blunt	254 mm	5/8" UNC
LPA224	Aluminum		12.7 mm	Sharp	457.2 mm	1/2" UNC
LPA224ST	Aluminum		12.7 mm	Blunt	457.2 mm	1/2" UNC
LPA242	Aluminum		15.88 mm	Sharp	304.8 mm	5/8" UNC
LPA242ST	Aluminum		15.88 mm	Blunt	304.8 mm	5/8" UNC
LPC201B	Copper	Bare	9.53 mm	Sharp	254 mm	3/8" UNC
LPC201BST	Copper	Bare	9.53 mm	Blunt	254 mm	3/8" UNC
LPC201ST	Copper	Nickel Plated	9.53 mm	Blunt	254 mm	3/8" UNC
LPC202	Copper	Nickel Plated	9.53 mm	Sharp	304.8 mm	3/8" UNC
LPC202B	Copper	Bare	9.53 mm	Sharp	304.8 mm	3/8" UNC
LPC202BST	Copper	Bare	9.53 mm	Blunt	304.8 mm	3/8" UNC
LPC202L	Copper	Tinned	9.53 mm	Sharp	304.8 mm	3/8" UNC
LPC202LST	Copper	Tinned	9.53 mm	Blunt	304.8 mm	3/8" UNC
LPC202ST	Copper	Nickel Plated	9.53 mm	Blunt	304.8 mm	3/8" UNC
LPA243	Aluminum		15.88 mm	Sharp	381 mm	5/8" UNC
LPA243ST	Aluminum		15.88 mm	Blunt	381 mm	5/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPA225	Aluminum		12.7 mm	Sharp	609.6 mm	1/2" UNC
LPA225ST	Aluminum		12.7 mm	Blunt	609.6 mm	1/2" UNC
LPC203	Copper	Nickel Plated	9.53 mm	Sharp	381 mm	3/8" UNC
LPC203B	Copper	Bare	9.53 mm	Sharp	381 mm	3/8" UNC
LPC203BST	Copper	Bare	9.53 mm	Blunt	381 mm	3/8" UNC
LPC203LST	Copper	Tinned	9.53 mm	Blunt	381 mm	3/8" UNC
LPC203ST	Copper	Nickel Plated	9.53 mm	Blunt	381 mm	3/8" UNC
LPA244	Aluminum		15.88 mm	Sharp	457.2 mm	5/8" UNC
LPA244ST	Aluminum		15.88 mm	Blunt	457.2 mm	5/8" UNC
LPA226	Aluminum		12.7 mm	Sharp	762 mm	1/2" UNC
LPA226ST	Aluminum		12.7 mm	Blunt	762 mm	1/2" UNC
LPC204	Copper	Nickel Plated	9.53 mm	Sharp	457.2 mm	3/8" UNC
LPC204B	Copper	Bare	9.53 mm	Sharp	457.2 mm	3/8" UNC
LPC204BST	Copper	Bare	9.53 mm	Blunt	457.2 mm	3/8" UNC
LPC204L	Copper	Tinned	9.53 mm	Sharp	457.2 mm	3/8" UNC
LPC204LST	Copper	Tinned	9.53 mm	Blunt	457.2 mm	3/8" UNC
LPC204ST	Copper	Nickel Plated	9.53 mm	Blunt	457.2 mm	3/8" UNC
LPC221	Copper	Nickel Plated	12.7 mm	Sharp	254 mm	1/2" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC221B	Copper	Bare	12.7 mm	Sharp	254 mm	1/2" UNC
LPC221BST	Copper	Bare	12.7 mm	Blunt	254 mm	1/2" UNC
LPC221L	Copper	Tinned	12.7 mm	Sharp	254 mm	1/2" UNC
LPC221LST	Copper	Tinned	12.7 mm	Blunt	254 mm	1/2" UNC
LPA227ST	Aluminum		12.7 mm	Blunt	914.4 mm	1/2" UNC
LPA245	Aluminum		15.88 mm	Sharp	609.6 mm	5/8" UNC
LPA245ST	Aluminum		15.88 mm	Blunt	609.6 mm	5/8" UNC
LPC221ST	Copper	Nickel Plated	12.7 mm	Blunt	254 mm	1/2" UNC
LPC222	Copper	Nickel Plated	12.7 mm	Sharp	304.8 mm	1/2" UNC
LPC222B	Copper	Bare	12.7 mm	Sharp	304.8 mm	1/2" UNC
LPC222BST	Copper	Bare	12.7 mm	Blunt	304.8 mm	1/2" UNC
LPC222L	Copper	Tinned	12.7 mm	Sharp	304.8 mm	1/2" UNC
LPC222LST	Copper	Tinned	12.7 mm	Blunt	304.8 mm	1/2" UNC
LPC222ST	Copper	Nickel Plated	12.7 mm	Blunt	304.8 mm	1/2" UNC
LPC205	Copper	Nickel Plated	9.53 mm	Sharp	609.6 mm	3/8" UNC
LPC205BST	Copper	Bare	9.53 mm	Blunt	609.6 mm	3/8" UNC
LPC205L	Copper	Tinned	9.53 mm	Sharp	609.6 mm	3/8" UNC
LPC205LST	Copper	Tinned	9.53 mm	Blunt	609.6 mm	3/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC205ST	Copper	Nickel Plated	9.53 mm	Blunt	609.6 mm	3/8" UNC
LPC206	Copper	Nickel Plated	9.53 mm	Sharp	762 mm	3/8" UNC
LPC206B	Copper	Bare	9.53 mm	Sharp	762 mm	3/8" UNC
LPC206BST	Copper	Bare	9.53 mm	Blunt	762 mm	3/8" UNC
LPC206L	Copper	Tinned	9.53 mm	Sharp	762 mm	3/8" UNC
LPC206LST	Copper	Tinned	9.53 mm	Blunt	762 mm	3/8" UNC
LPC206ST	Copper	Nickel Plated	9.53 mm	Blunt	762 mm	3/8" UNC
LPC207	Copper	Nickel Plated	9.53 mm	Sharp	914.4 mm	3/8" UNC
LPC207B	Copper	Bare	9.53 mm	Sharp	914.4 mm	3/8" UNC
LPC207BST	Copper	Bare	9.53 mm	Blunt	914.4 mm	3/8" UNC
LPC207LST	Copper	Tinned	9.53 mm	Blunt	914.4 mm	3/8" UNC
LPC207ST	Copper	Nickel Plated	9.53 mm	Blunt	914.4 mm	3/8" UNC
LPC208	Copper	Nickel Plated	9.53 mm	Sharp	1219.2 mm	3/8" UNC
LPC208B	Copper	Bare	9.53 mm	Sharp	1219.2 mm	3/8" UNC
LPC208BST	Copper	Bare	9.53 mm	Blunt	1219.2 mm	3/8" UNC
LPC208L	Copper	Tinned	9.53 mm	Sharp	1219.2 mm	3/8" UNC
LPC208LST	Copper	Tinned	9.53 mm	Blunt	1219.2 mm	3/8" UNC
LPC208ST	Copper	Nickel Plated	9.53 mm	Blunt	1219.2 mm	3/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPA246	Aluminum		15.88 mm	Sharp	762 mm	5/8" UNC
LPA246ST	Aluminum		15.88 mm	Blunt	762 mm	5/8" UNC
LPC223	Copper	Nickel Plated	12.7 mm	Sharp	381 mm	1/2" UNC
LPC223B	Copper	Bare	12.7 mm	Sharp	381 mm	1/2" UNC
LPC223BST	Copper	Bare	12.7 mm	Blunt	381 mm	1/2" UNC
LPC223L	Copper	Tinned	12.7 mm	Sharp	381 mm	1/2" UNC
LPC223LST	Copper	Tinned	12.7 mm	Blunt	381 mm	1/2" UNC
LPC223ST	Copper	Nickel Plated	12.7 mm	Blunt	381 mm	1/2" UNC
LPA228	Aluminum		12.7 mm	Sharp	1219.2 mm	1/2" UNC
LPA228ST	Aluminum		12.7 mm	Blunt	1219.2 mm	1/2" UNC
LPC241	Copper	Nickel Plated	15.88 mm	Sharp	254 mm	5/8" UNC
LPC241B	Copper	Bare	15.88 mm	Sharp	254 mm	5/8" UNC
LPC241BST	Copper	Bare	15.88 mm	Blunt	254 mm	5/8" UNC
LPC241ST	Copper	Nickel Plated	15.88 mm	Blunt	254 mm	5/8" UNC
LPC242	Copper	Nickel Plated	15.88 mm	Sharp	304.8 mm	5/8" UNC
LPS222	Stainless Steel 304 (EN 1.4301)		12.7 mm	Sharp	304.8 mm	1/2" UNC
LPA247	Aluminum		15.88 mm	Sharp	914.4 mm	5/8" UNC
LPA247ST	Aluminum		15.88 mm	Blunt	914.4 mm	5/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC224	Copper	Nickel Plated	12.7 mm	Sharp	457.2 mm	1/2" UNC
LPC224B	Copper	Bare	12.7 mm	Sharp	457.2 mm	1/2" UNC
LPC224BST	Copper	Bare	12.7 mm	Blunt	457.2 mm	1/2" UNC
LPC224L	Copper	Tinned	12.7 mm	Sharp	457.2 mm	1/2" UNC
LPC224LST	Copper	Tinned	12.7 mm	Blunt	457.2 mm	1/2" UNC
LPC224ST	Copper	Nickel Plated	12.7 mm	Blunt	457.2 mm	1/2" UNC
LPC225	Copper	Nickel Plated	12.7 mm	Sharp	609.6 mm	1/2" UNC
LPC225B	Copper	Bare	12.7 mm	Sharp	609.6 mm	1/2" UNC
LPC225BST	Copper	Bare	12.7 mm	Blunt	609.6 mm	1/2" UNC
LPC225L	Copper	Tinned	12.7 mm	Sharp	609.6 mm	1/2" UNC
LPC225LST	Copper	Tinned	12.7 mm	Blunt	609.6 mm	1/2" UNC
LPC225ST	Copper	Nickel Plated	12.7 mm	Blunt	609.6 mm	1/2" UNC
LPC226	Copper	Nickel Plated	12.7 mm	Sharp	762 mm	1/2" UNC
LPC226B	Copper	Bare	12.7 mm	Sharp	762 mm	1/2" UNC
LPC226BST	Copper	Bare	12.7 mm	Blunt	762 mm	1/2" UNC
LPC226L	Copper	Tinned	12.7 mm	Sharp	762 mm	1/2" UNC
LPC226LST	Copper	Tinned	12.7 mm	Blunt	762 mm	1/2" UNC
LPC226ST	Copper	Nickel Plated	12.7 mm	Blunt	762 mm	1/2" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC227	Copper	Nickel Plated	12.7 mm	Sharp	914.4 mm	1/2" UNC
LPC227B	Copper	Bare	12.7 mm	Sharp	914.4 mm	1/2" UNC
LPC227BST	Copper	Bare	12.7 mm	Blunt	914.4 mm	1/2" UNC
LPC227L	Copper	Tinned	12.7 mm	Sharp	914.4 mm	1/2" UNC
LPC227LST	Copper	Tinned	12.7 mm	Blunt	914.4 mm	1/2" UNC
LPC227ST	Copper	Nickel Plated	12.7 mm	Blunt	914.4 mm	1/2" UNC
LPC228	Copper	Nickel Plated	12.7 mm	Sharp	1219.2 mm	1/2" UNC
LPC228BST	Copper	Bare	12.7 mm	Blunt	1219.2 mm	1/2" UNC
LPC228L	Copper	Tinned	12.7 mm	Sharp	1219.2 mm	1/2" UNC
LPC228LST	Copper	Tinned	12.7 mm	Blunt	1219.2 mm	1/2" UNC
LPC228ST	Copper	Nickel Plated	12.7 mm	Blunt	1219.2 mm	1/2" UNC
LPS225	Stainless Steel 304 (EN 1.4301)		12.7 mm	Sharp	609.6 mm	1/2" UNC
LPS225ST	Stainless Steel 304 (EN 1.4301)		12.7 mm	Blunt	609.6 mm	1/2" UNC
LPS226	Stainless Steel 304 (EN 1.4301)		12.7 mm	Sharp	762 mm	1/2" UNC
LPS227	Stainless Steel 304 (EN 1.4301)		12.7 mm	Sharp	914.4 mm	1/2" UNC
LPS227ST	Stainless Steel 304 (EN 1.4301)		12.7 mm	Blunt	914.4 mm	1/2" UNC
LPS228	Stainless Steel 304 (EN 1.4301)		12.7 mm	Sharp	1219.2 mm	1/2" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC242B	Copper	Bare	15.88 mm	Sharp	304.8 mm	5/8" UNC
LPC242BST	Copper	Bare	15.88 mm	Blunt	304.8 mm	5/8" UNC
LPC242L	Copper	Tinned	15.88 mm	Sharp	304.8 mm	5/8" UNC
LPC242LST	Copper	Tinned	15.88 mm	Blunt	304.8 mm	5/8" UNC
LPC242ST	Copper	Nickel Plated	15.88 mm	Blunt	304.8 mm	5/8" UNC
LPC243	Copper	Nickel Plated	15.88 mm	Sharp	381 mm	5/8" UNC
LPC243B	Copper	Bare	15.88 mm	Sharp	381 mm	5/8" UNC
LPA248	Aluminum		15.88 mm	Sharp	1219.2 mm	5/8" UNC
LPA248ST	Aluminum		15.88 mm	Blunt	1219.2 mm	5/8" UNC
LPC243BST	Copper	Bare	15.88 mm	Blunt	381 mm	5/8" UNC
LPC243ST	Copper	Nickel Plated	15.88 mm	Blunt	381 mm	5/8" UNC
LPC244	Copper	Nickel Plated	15.88 mm	Sharp	457.2 mm	5/8" UNC
LPC244B	Copper	Bare	15.88 mm	Sharp	457.2 mm	5/8" UNC
LPC244BST	Copper	Bare	15.88 mm	Blunt	457.2 mm	5/8" UNC
LPC244L	Copper	Tinned	15.88 mm	Sharp	457.2 mm	5/8" UNC
LPC244LST	Copper	Tinned	15.88 mm	Blunt	457.2 mm	5/8" UNC
LPC244MBST	Copper	Bare	15.88 mm	Blunt	500.38 mm	5/8" UNC
LPC244ST	Copper	Nickel Plated	15.88 mm	Blunt	457.2 mm	5/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC245	Copper	Nickel Plated	15.88 mm	Sharp	609.6 mm	5/8" UNC
LPC245B	Copper	Bare	15.88 mm	Sharp	609.6 mm	5/8" UNC
LPC245BST	Copper	Bare	15.88 mm	Blunt	609.6 mm	5/8" UNC
LPC245L	Copper	Tinned	15.88 mm	Sharp	609.6 mm	5/8" UNC
LPC245LST	Copper	Tinned	15.88 mm	Blunt	609.6 mm	5/8" UNC
LPC245ST	Copper	Nickel Plated	15.88 mm	Blunt	609.6 mm	5/8" UNC
LPC246	Copper	Nickel Plated	15.88 mm	Sharp	762 mm	5/8" UNC
LPC246B	Copper	Bare	15.88 mm	Sharp	762 mm	5/8" UNC
LPC246BST	Copper	Bare	15.88 mm	Blunt	762 mm	5/8" UNC
LPC246ST	Copper	Nickel Plated	15.88 mm	Blunt	762 mm	5/8" UNC
LPC247	Copper	Nickel Plated	15.88 mm	Sharp	914.4 mm	5/8" UNC
LPC247B	Copper	Bare	15.88 mm	Sharp	914.4 mm	5/8" UNC
LPC247BST	Copper	Bare	15.88 mm	Blunt	914.4 mm	5/8" UNC
LPC247L	Copper	Tinned	15.88 mm	Sharp	914.4 mm	5/8" UNC
LPC247LST	Copper	Tinned	15.88 mm	Blunt	914.4 mm	5/8" UNC
LPC247MBST	Copper	Bare	15.88 mm	Blunt	1000.76 mm	5/8" UNC
LPC247ST	Copper	Nickel Plated	15.88 mm	Blunt	914.4 mm	5/8" UNC
LPC248	Copper	Nickel Plated	15.88 mm	Sharp	1219.2 mm	5/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPC248B	Copper	Bare	15.88 mm	Sharp	1219.2 mm	5/8" UNC
LPC248BST	Copper	Bare	15.88 mm	Blunt	1219.2 mm	5/8" UNC
LPC248L	Copper	Tinned	15.88 mm	Sharp	1219.2 mm	5/8" UNC
LPC248ST	Copper	Nickel Plated	15.88 mm	Blunt	1219.2 mm	5/8" UNC
LPC415	Copper	Bare	15.88 mm	Sharp	1524 mm	5/8" UNC
LPC416	Copper	Bare	15.88 mm	Sharp	1828.8 mm	5/8" UNC
LPC417	Copper	Bare	15.88 mm	Sharp	2133.6 mm	5/8" UNC
LPC418	Copper	Bare	15.88 mm	Sharp	2438.4 mm	5/8" UNC
LPS411	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	457.2 mm	5/8" UNC
LPS412	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	609.6 mm	5/8" UNC
LPS413	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	914.4 mm	5/8" UNC
LPS414	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	1219.2 mm	5/8" UNC
LPS415	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	1524 mm	5/8" UNC
LPS416	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	1828.8 mm	5/8" UNC
LPS417	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	2133.6 mm	5/8" UNC
LPS418	Stainless Steel 304 (EN 1.4301)		15.88 mm	Sharp	2438.4 mm	5/8" UNC

CatalogNumber	Material	Finish	Diameter (Ø)	Type	Height (H)	Thread Size (TS)
LPS421	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	457.2 mm	5/8" UNC
LPS423	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	914.4 mm	5/8" UNC
LPS425	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	1524 mm	5/8" UNC
LPS426	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	1828.8 mm	5/8" UNC
LPS424	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	1219.2 mm	5/8" UNC
LPS427	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	2133.6 mm	5/8" UNC
LPS428	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	2438.4 mm	5/8" UNC
LPS422	Stainless Steel 304 (EN 1.4301)		19.1 mm	Sharp	609.6 mm	5/8" UNC
LPC421	Copper	Bare	19.05 mm	Sharp	457.2 mm	5/8" UNC
LPC422	Copper	Bare	19.05 mm	Sharp	609.6 mm	5/8" UNC
LPC423	Copper	Bare	19.05 mm	Sharp	914.4 mm	5/8" UNC
LPC424	Copper	Bare	19.05 mm	Sharp	1219.2 mm	5/8" UNC
LPC425	Copper	Bare	19.05 mm	Sharp	1524 mm	5/8" UNC
LPC426	Copper	Bare	19.05 mm	Sharp	1828.8 mm	5/8" UNC
LPC427	Copper	Bare	19.05 mm	Sharp	2133.6 mm	5/8" UNC
LPC428	Copper	Bare	19.05 mm	Sharp	2438.4 mm	5/8" UNC

Table 2/2

Catalog Number	Unit Weight	Certifications
LPA221	0.09 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA221ST	0.09 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA222	0.1 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA222ST	0.1 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA223	0.13 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA223ST	0.13 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA241	0.14 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA241ST	0.14 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA224	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA224ST	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA242	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA242ST	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC201B	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC201BST	0.16 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC201ST	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC202	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC202B	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC202BST	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC202L	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC202LST	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC202ST	0.19 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA243	0.2 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA243ST	0.2 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA225	0.21 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA225ST	0.21 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC203	0.23 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC203B	0.23 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC203BST	0.23 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC203LST	0.23 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC203ST	0.23 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA244	0.25 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA244ST	0.25 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA226	0.26 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA226ST	0.26 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC204	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC204B	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC204BST	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC204L	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC204LST	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC204ST	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221B	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221BST	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221L	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221LST	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA227ST	0.31 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA245	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA245ST	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC221ST	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC222	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC222B	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC222BST	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC222L	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC222LST	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC222ST	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC205	0.37 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC205BST	0.37 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC205L	0.37 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC205LST	0.37 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC205ST	0.37 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206B	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206BST	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206L	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206LST	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC206ST	0.47 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC207	0.56 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC207B	0.56 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC207BST	0.56 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC207LST	0.56 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC207ST	0.56 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC208	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC208B	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC208BST	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC208L	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC208LST	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC208ST	0.75 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA246	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA246ST	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223B	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223BST	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223L	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223LST	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC223ST	0.41 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA228	0.42 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA228ST	0.42 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC241	0.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC241B	0.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC241BST	0.43 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC241ST	0.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC242	0.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS222	0.48 kg	
LPA247	0.49 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA247ST	0.49 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224B	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224BST	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224L	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224LST	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC224ST	0.5 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225B	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225BST	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225L	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225LST	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC225ST	0.66 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC226	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC226B	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC226BST	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC226L	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC226LST	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC226ST	0.83 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227B	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227BST	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227L	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227LST	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC227ST	0.99 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC228	1.32 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC228BST	1.32 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC228L	1.32 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC228LST	1.32 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC228ST	1.32 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS225	0.95 kg	
LPS225ST	0.95 kg	


Catalog Number	Unit Weight	Certifications
LPS226	1.19 kg	
LPS227	1.43 kg	
LPS227ST	1.43 kg	
LPS228	1.9 kg	
LPC242B	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC242BST	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC242L	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC242LST	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC242ST	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC243	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC243B	0.52 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA248	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA248ST	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC243BST	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC243ST	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244B	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244BST	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC244L	0.65 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244LST	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244MBST	0.85 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC244ST	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245B	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245BST	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245L	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245LST	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC245ST	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC246	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC246B	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC246BST	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC246ST	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247	1.29 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247B	1.29 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247BST	1.29 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247L	1.29 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPC247LST	1.29 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247MBST	1.7 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC247ST	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC248	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC248B	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC248BST	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC248L	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC248ST	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC415	2.59 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC416	3.1 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC417	3.62 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC418	4.14 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS411	0.71 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS412	0.95 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS413	1.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS414	1.9 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS415	2.38 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS416	2.85 kg	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Unit Weight	Certifications
LPS417	3.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS418	3.81 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS421	0.71 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS423	1.43 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS425	2.38 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS426	2.85 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS424	1.9 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS427	3.33 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS428	3.81 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPS422	0.95 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC421	0.78 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC422	1.03 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC423	1.55 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC424	2.07 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC425	2.59 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC426	3.1 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC427	3.62 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC428	4.14 kg	E202878-Combined_CoC, E202878-Combined_CoC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE