

# Rail Base Track Circuit Dual Shunt, T-Handle



## FEATURES

One easy-to-carry assembly that can be used on most common rail types

Two shunts in one assembly: "Hard" zero ohm and 0.06 ohm

No resistor to fail: Product is pre-engineered to provide permanent 0.06 ohm shunting

Tested to assure reliability of 0.06 ohm shunt

Orange insulation for high visibility

Cable welded to terminal clamp

Hardened contact points on clamps bite through rust and scale

Unique design assures positive contact and firm grip

T-shaped handle allows quick and easy tightening by hand

## SPECIFICATIONS

**Material:** Cadmium Bronze;Steel;Polyvinylchloride

**Color:** Orange

Table 1/2

| Catalog Number | Length (L) | Width (W) | Height (H) | Rail Foot Thickness (RFT) | Shunt                             | Conductor Size                   |
|----------------|------------|-----------|------------|---------------------------|-----------------------------------|----------------------------------|
| SBB2721S       | 2184mm     | 25.4 mm   | 47.6 mm    | 15.24 mm Max              | Hard (Zero Ohm), Tuned (0.06 Ohm) | 3/16" Bondstrand, 5/32" Stranded |


| CatalogNumber | Length (L) | Width (W) | Height (H) | Rail Foot Thickness (RFT) | Shunt                             | Conductor Size                   |
|---------------|------------|-----------|------------|---------------------------|-----------------------------------|----------------------------------|
| SBB2721B      | 2184mm     | 25.4 mm   | 47.6 mm    | 15.24 mm Max              | Hard (Zero Ohm), Tuned (0.06 Ohm) | 3/16" Bondstrand, 5/32" Stranded |

| Table 2/2      |                          |
|----------------|--------------------------|
| Catalog Number | Number of Contact Points |
| SBB2721S       | 2                        |
| SBB2721B       | 3                        |

### ADDITIONAL PRODUCT DETAILS

In order to meet the electrical requirements of 0.06 Ohms, the manufactured length may be longer than the indicated length.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**