


305 Stainless Steel Beam Clamp, Top Mount



CERTIFICATIONS



FEATURES

Pressed steel beam clamp

Structural attachment to top flange of metal beams, purlins, channel, or angle iron

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19)

SPECIFICATIONS

Material: Stainless Steel 304 (EN 1.4301)

Table 1/2

Catalog Number	Rod Size (RS)	Flange Thickness (FT)	A	Screw Diameter (Sc)	Screw Length (L)	Torque (TQ)
3050037S4	3/8"	5/8" Max	7/8"	3/8"	1 1/2"	5 ft·lbf
3050050S4	1/2"	5/8" Max	7/8"	3/8"	1 1/2"	5 ft·lbf


Table 2/2

Catalog Number	Static Load (F)
3050037S4	500lb
3050050S4	1130lb

ADDITIONAL PRODUCT DETAILS

Set screw must be tightened and torqued onto the sloped side of the I-beam, channel, or angle iron flange.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

