

# B18-EM Box/Conduit Hanger with Flange Clip



## CERTIFICATIONS



## FEATURES

One assembly provides support for electrical box and/or conduit from beam flanges

Eliminates need for offset bending conduit

66% less Drop Wires (rod/wire application)

NEC® & CEC compliant

## SPECIFICATIONS

**Finish:** nVent CADDY Armour

**Material:** Spring Steel

Table 1/1

Catalog Number	EMT Conduit Size	Flange Thickness	Flexible Conduit Size	MC/AC Cable Size
16MB1824	3/4", 1"	1/8"		
6MB1824		1/8"	3/8"	14-2 to 12-3

Catalog Number	EMT Conduit Size	Flange Thickness	Flexible Conduit Size	MC/AC Cable Size
812MB1824	1/2", 3/4"	1/8"		
16MB1858	3/4", 1"	5/16" - 1/2"		
6MB1858		5/16" - 1/2"	3/8"	14-2 to 12-3
812MB1858	1/2", 3/4"	5/16" - 1/2"		

## ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

