

# **PH Multi-Purpose Purlin Clamp**



### **CERTIFICATIONS**





#### **FEATURES**

Attaches to bottom of purlins and beams to support threaded rod

### **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel

Table 1/2							
Catalog Number	Rod Size (RS)	Flange Thickness (FT)	В	Torque (TQ)	Static Load 1 (F1)	Static Load 2 (F2)	
PH4	1/4"	1/4" Max	3/4" Min	30 ft·lbf	200lb	160lb	
PH6FP	3/8"	1/4" Max	3/4" Min	30 ft·lbf	200lb		
PH6	3/8"	1/4" Max	3/4" Min	30 ft·lbf	200lb	160lb	


Table 2/2				
Catalog Number	Nut Included			
PH4	No			
PH6FP	Yes			
PH6	No			


#### ADDITIONAL PRODUCT DETAILS

A jam nut is required for fire protection applications.

Refer to Static Load 1 when attaching to C and Z purlins. Refer to Static Load 2 when attaching to a flat flange.

## **DIAGRAMS**





## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

