


Snap Close Conduit/Pipe Clamp



The nVent CADDY Snap Close Conduit Clamps (M-Series) are a fast and efficient method to secure conduit branch circuits for electrical installations. The M-Series is designed to provide positional consistency in application by eliminating conduit offset as well as maintain spacing entering electrical boxes. Increase installation efficiency by utilizing our comprehensive conduit range for your next electrical project.

CERTIFICATIONS



FEATURES

May be used for either vertical or horizontal installations

Eliminates need for offset bending conduit

Finger closure, no tools required

Locking design has greater resistance to twisting loads and is stronger than any on the market

Low profile locking tabs and smooth gripping dimples remove the possibility of scrapes

812M and 16M feature double tabs to center conduit, increase range and holding power and prevent conduit from sliding

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/2


Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Hole Size (HS)
----------------	-----------------------	------------------	------------------	-------------------------	---------------------	----------------

16M4I			3/4", 1"	3/4", 1"	0.920" - 1.38"	1/4"
20M4I			1 1/4"	1 1/4"	1.380" - 1.65"	1/4"
24M4I			1 1/2"	1 1/2"	1.650" - 1.97"	1/4"
32M4I			2"	2"	1.970" - 2.36"	1/4"
6M4I	3/8"	14-2 to 12-3			0.550" - 0.71"	1/4"
812M4I			1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	1/4"
16M			3/4", 1"	3/4", 1"	0.920" - 1.38"	9/32"
20M			1 1/4"	1 1/4"	1.380" - 1.65"	9/32"
24M			1 1/2"	1 1/2"	1.650" - 1.97"	9/32"
32M			2"	2"	1.970" - 2.36"	9/32"
6M	3/8"	14-2 to 12-3			0.550" - 0.71"	9/32"
812M			1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	9/32"

Table 2/2			
Catalog Number	Hole Type	Static Load 1 (F1)	Static Load 2 (F2)
16M4I	Threaded	100lb	25lb
20M4I	Threaded	100lb	25lb
24M4I	Threaded	100lb	25lb
32M4I	Threaded	100lb	25lb
6M4I	Threaded	100lb	25lb

Catalog Number	Hole Type	Static Load 1 (F1)	Static Load 2 (F2)
812M4I	Threaded	100lb	25lb
16M	Plain	100lb	25lb
20M	Plain	100lb	25lb
24M	Plain	100lb	25lb
32M	Plain	100lb	25lb
6M	Plain	100lb	25lb
812M	Plain	100lb	25lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

