

1 Hole Lug, GL Style

Data Solutions



FEATURES

Provides an efficient bolting surface for grounding and power applications

Electrolytic grade copper

For use with nVent ERICO Cadweld type GL connections only

SPECIFICATIONS

Material: Copper

Type: NEMA®

Finish: Tinned

Table 1/2

Catalog Number	Height (H)	Length (L)	Width (W)	Thickness (T)	A	Hole Size (HS)
B121CE	0.44in	1.44in	1in	0.12in	0.62in	0.56in
B121QQ	0.43in	1.52in	1in	0.13in	0.63in	0.56in
B121SQ	0.43in	1.44in	1in	0.19in	0.63in	0.55in
B121DE	0.44in	1.47in	1in	0.19in	0.62in	0.56in

CatalogNumber	Height (H)	Length (L)	Width (W)	Thickness (T)	A	Hole Size (HS)
B121EG	0.44in	1.5in	1.5in	0.25in	0.62in	0.56in
B121EE	0.44in	1.5in	1in	0.25in	0.62in	0.56in



Table 2/2

Catalog Number	Angle (a)	Equivalent Conductor Size
B121CE	90°	159.12kcmil
B121QQ	90°	159kcmil
B121SQ	90°	239kcmil
B121DE	105°	238.69kcmil
B121EG	135°	477.38kcmil
B121EE	135°	318.25kcmil

ADDITIONAL PRODUCT DETAILS

For sizes not listed, contact us.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE