


Cable to Ground Rod Splice/Grounding Receptacle

Data Solutions



nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CERTIFICATIONS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

SPECIFICATIONS

Table 1/2

| Catalog Number | Ground Rod Type | Mold Family | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size | Conductor Outer Diameter, Nominal |
|----------------|-----------------|-------------|------------------------------|-----------------------------|----------------|-----------------------------------|
|----------------|-----------------|-------------|------------------------------|-----------------------------|----------------|-----------------------------------|

| | | | | | | |
|------------------|---------------|--|---------|--------|----------------|--------|
| GBJGT161HR1 | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | #6 Concentric | 0.18in |
| GBJGT181HR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | #6 Concentric | 0.18in |
| GBJGT181LR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | #4 Concentric | 0.23in |
| GBJGT181LR1 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | #4 Concentric | 0.23in |
| RAC1L2Q | | RA (To Ground Plate) Mold Family | | | #4 Concentric | 0.23in |
| RBC1L | | RB (To Grounding Receptacle) Mold Family | | | #4 Concentric | 0.23in |
| GBJGT181VR2 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | #2 Concentric | 0.29in |
| GBJGT181VR2 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | #2 Concentric | 0.29in |
| GBJGR162CR2 | Copper-bonded | GB/GR Mold Family | 0.625in | 0.56in | 1/0 Concentric | 0.37in |
| GBJGR182CR1 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| GBJGR182CR1 M | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| GBJGR182CR2 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| GBJGR182CR2 M | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| GBJGT162CR1 M | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | 1/0 Concentric | 0.37in |
| GBJGT182CR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| GBJGT182CR1 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |

| | | | | | | |
|---------------|---------------|--|---------|--------|----------------|--------|
| GBJGT182CR3 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 1/0 Concentric | 0.37in |
| RAC2C | | RA (To Grounding Receptacle) Mold Family | | | 1/0 Concentric | 0.37in |
| RAC2C2Q | | RA (To Ground Plate) Mold Family | | | 1/0 Concentric | 0.37in |
| RBC2C2Q | | RB (To Ground Plate) Mold Family | | | 1/0 Concentric | 0.37in |
| GECP100 | Steel | GE Mold Family | 10in | 0.39in | | |
| GECP107P107 | Steel | GE Mold Family | 10.7in | 0.42in | | |
| GBJGR182GR1 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 2/0 Concentric | 0.42in |
| GBJGR182GR2 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 2/0 Concentric | 0.42in |
| GBJGR182GR2 M | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 2/0 Concentric | 0.42in |
| GBJGR332GR1 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.75in | 2/0 Concentric | 0.42in |
| GBJGT162GR1 | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | 2/0 Concentric | 0.42in |
| GBJGT162GR1 M | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | 2/0 Concentric | 0.42in |
| GBJGT182GR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 2/0 Concentric | 0.42in |
| GBJGT182GR1 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 2/0 Concentric | 0.42in |
| GBJGT332GR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.75in | 2/0 Concentric | 0.42in |
| RAC2G | | RA (To Grounding Receptacle) Mold Family | | | 2/0 Concentric | 0.42in |

| | | | | | | |
|--------------|---------------|--|---------|--------|-------------------------------|--------|
| RAC2G2Q | | RA (To Ground Plate) Mold Family | | | 2/0 Concentric | 0.42in |
| RAC2G3Q | | RA (To Ground Plate) Mold Family | | | 2/0 Concentric | 0.42in |
| RBC2G | | RB (To Grounding Receptacle) Mold Family | | | 2/0 Concentric | 0.42in |
| RBC2G2Q | | RB (To Ground Plate) Mold Family | | | 2/0 Concentric | 0.42in |
| RBC2G3Q | | RB (To Ground Plate) Mold Family | | | 2/0 Concentric | 0.42in |
| RACY4 | | RA (To Grounding Receptacle) Mold Family | | | 70 mm ² Concentric | 0.43in |
| RACY42Q | | RA (To Ground Plate) Mold Family | | | 70 mm ² Concentric | 0.43in |
| GECP120DBG | Steel | GE Mold Family | 12in | 0.47in | | |
| GBJGR182LR1 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 3/0 Concentric | 0.47in |
| GBJGT162LR1 | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | 3/0 Concentric | 0.47in |
| GBJGT182LR1M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 3/0 Concentric | 0.47in |
| GBJGT182LR2 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 3/0 Concentric | 0.47in |
| RAC2L2Q | | RA (To Ground Plate) Mold Family | | | 3/0 Concentric | 0.47in |
| GEC14 | Steel | GE Mold Family | 0.5in | 0.51in | | |
| GFCY5DBG | | GF (To Ground Plate) Mold family | | | 95 mm ² Concentric | 0.51in |
| GBJGR162QR1 | Copper-bonded | GB/GR Mold Family | 0.625in | 0.56in | 4/0 Concentric | 0.53in |

| | | | | | | |
|------------------|---------------|--|---------|--------|--------------------------------|--------|
| GBJGR182QR1 | Copper-bonded | GB/GR Mold Family | 0.75in | 0.68in | 4/0 Concentric | 0.53in |
| GBJGT162QR1 M | Copper-bonded | GB/GT Mold Family | 0.625in | 0.56in | 4/0 Concentric | 0.53in |
| GBJGT182QR1 | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 4/0 Concentric | 0.53in |
| GBJGT182QR2 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.68in | 4/0 Concentric | 0.53in |
| GBJGT332QR1 M | Copper-bonded | GB/GT Mold Family | 0.75in | 0.75in | 4/0 Concentric | 0.53in |
| RAC2Q | | RA (To Grounding Receptacle) Mold Family | | | 4/0 Concentric | 0.53in |
| RAC2Q2Q | | RA (To Ground Plate) Mold Family | | | 4/0 Concentric | 0.53in |
| RBC2Q | | RB (To Grounding Receptacle) Mold Family | | | 4/0 Concentric | 0.53in |
| RBC2Q2Q | | RB (To Ground Plate) Mold Family | | | 4/0 Concentric | 0.53in |
| GBR16R1 | Copper-bonded | GB Mold Family | 0.625in | 0.56in | | |
| GEC16 | Copper-bonded | GE Mold Family | 0.625in | 0.56in | | |
| GFC2VDBG | | GF (To Ground Plate) Mold family | | | 250 kcmil Concentric | 0.57in |
| RAC2V2Q | | RA (To Ground Plate) Mold Family | | | 250 kcmil Concentric | 0.57in |
| RACY62Q | | RA (To Ground Plate) Mold Family | | | 120 mm ² Concentric | 0.57in |
| GECP150 | Steel | GE Mold Family | 15in | 0.59in | | |

| | | | | | | |
|----------|---------------|----------------------------------|---------|--------|----------------------|--------|
| GEC31 | Steel | GE Mold Family | 0.625in | 0.62in | | |
| GECP160 | Steel | GE Mold Family | 16in | 0.63in | | |
| GBR18R1 | Copper-bonded | GB Mold Family | 0.75in | 0.68in | | |
| GBR18R2 | Copper-bonded | GB Mold Family | 0.75in | 0.68in | | |
| GEC18 | Copper-bonded | GE Mold Family | 0.75in | 0.68in | | |
| GFC3DDBG | | GF (To Ground Plate) Mold family | | | 350 kcmil Concentric | 0.68in |
| GBR33R1 | Steel | GB Mold Family | 0.75in | 0.75in | | |
| GBF22R1 | Copper-bonded | GB Mold Family | 1in | 0.91in | | |

Table 2/2

| Catalog Number | Connects To | Ground Plate/Grounding Receptacle | Certifications |
|----------------|-------------|-----------------------------------|----------------|
| GBJGT161HR1 | | B165 Grounding Receptacle | cUL, UL |
| GBJGT181HR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT181LR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT181LR1M | | B165 Grounding Receptacle | cUL, UL |
| RAC1L2Q | | 4/0 Ground Plate | cUL, UL |
| RBC1L | | B165 Grounding Receptacle | UL, cUL |
| GBJGT181VR2 | | B166 Grounding Receptacle | UL, cUL |
| GBJGT181VR2M | | B166 Grounding Receptacle | cUL, UL |
| GBJGR162CR2 | | B166 Grounding Receptacle | cUL, UL |

| Catalog Number | Connects To | Ground Plate/Grounding Receptacle | Certifications |
|----------------|----------------------|-----------------------------------|----------------|
| GBJGR182CR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGR182CR1M | | B165 Grounding Receptacle | UL, cUL |
| GBJGR182CR2 | | B166 Grounding Receptacle | UL, cUL |
| GBJGR182CR2M | | B166 Grounding Receptacle | cUL, UL |
| GBJGT162CR1M | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182CR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182CR1M | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182CR3 | | B167 Grounding Receptacle | UL, cUL |
| RAC2C | | B165 Grounding Receptacle | UL, cUL |
| RAC2C2Q | | 4/0 Ground Plate | UL, cUL |
| RBC2C2Q | | 4/0 Ground Plate | UL, cUL |
| GECP100 | Identical Ground Rod | | |
| GECP107P107 | Identical Ground Rod | | |
| GBJGR182GR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGR182GR2 | | B166 Grounding Receptacle | cUL, UL |
| GBJGR182GR2M | | B166 Grounding Receptacle | UL, cUL |
| GBJGR332GR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT162GR1 | | B165 Grounding Receptacle | UL, cUL |

| Catalog Number | Connects To | Ground Plate/Grounding Receptacle | Certifications |
|----------------|-------------|-----------------------------------|----------------|
| GBJGT162GR1M | | B165 Grounding Receptacle | cUL, UL |
| GBJGT182GR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182GR1M | | B165 Grounding Receptacle | cUL, UL |
| GBJGT332GR1 | | B165 Grounding Receptacle | cUL, UL |
| RAC2G | | B165 Grounding Receptacle | cUL, UL |
| RAC2G2Q | | 4/0 Ground Plate | UL, cUL |
| RAC2G3Q | | 500 kcmil Ground Plate | cUL, UL |
| RBC2G | | B165 Grounding Receptacle | cUL, UL |
| RBC2G2Q | | 4/0 Ground Plate | UL, cUL |
| RBC2G3Q | | 500 kcmil Ground Plate | |
| RACY4 | | B165 Grounding Receptacle | cUL, UL |
| RACY42Q | | 4/0 Ground Plate | UL, cUL |
| GECP120DBG | | DB Ground Plate | |
| GBJGR182LR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT162LR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182LR1M | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182LR2 | | B166 Grounding Receptacle | UL, cUL |
| RAC2L2Q | | 4/0 Ground Plate | UL, cUL |

| Catalog Number | Connects To | Ground Plate/Grounding Receptacle | Certifications |
|----------------|----------------------|-----------------------------------|----------------|
| GEC14 | Identical Ground Rod | | |
| GFCY5DBG | | DB Ground Plate | |
| GBJGR162QR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGR182QR1 | | B165 Grounding Receptacle | cUL, UL |
| GBJGT162QR1M | | B165 Grounding Receptacle | cUL, UL |
| GBJGT182QR1 | | B165 Grounding Receptacle | UL, cUL |
| GBJGT182QR2M | | B166 Grounding Receptacle | UL, cUL |
| GBJGT332QR1M | | B165 Grounding Receptacle | UL, cUL |
| RAC2Q | | B165 Grounding Receptacle | UL, cUL |
| RAC2Q2Q | | 4/0 Ground Plate | cUL, UL |
| RBC2Q | | B165 Grounding Receptacle | UL, cUL |
| RBC2Q2Q | | 4/0 Ground Plate | UL, cUL |
| GBR16R1 | | B165 Grounding Receptacle | UL, cUL |
| GEC16 | Identical Ground Rod | | |
| GFC2VDBG | | DB Ground Plate | |
| RAC2V2Q | | 4/0 Ground Plate | UL, cUL |
| RACY62Q | | 4/0 Ground Plate | UL, cUL |
| GECP150 | Identical Ground Rod | | |

| Catalog Number | Connects To | Ground Plate/Grounding Receptacle | Certifications |
|----------------|----------------------|-----------------------------------|----------------|
| GEC31 | Identical Ground Rod | | |
| GECP160 | Identical Ground Rod | | |
| GBR18R1 | | B165 Grounding Receptacle | UL, cUL |
| GBR18R2 | | B166 Grounding Receptacle | UL, cUL |
| GEC18 | Identical Ground Rod | | |
| GFC3DDBG | | DB Ground Plate | |
| GBR33R1 | | B165 Grounding Receptacle | cUL, UL |
| GBF22R1 | | B165 Grounding Receptacle | UL, cUL |

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

| XX-X-XX-XX-XX-XX-L-M-W | | |
|------------------------|----------------------|---|
| XX | Mold Family | |
| X | Price Key | |
| XX | Mold Family | |
| XX | Ground Rod Type | |
| XX | Conductor Code | |
| XX | Grounding Receptacle | |
| L* | Split Crucible | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M* | Mold Only | |
| W* | Wear Plates | Reduce mechanical abrasion of molds at cable entry points |

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE