

315 Malleable Iron Purlin Clamp



CERTIFICATIONS



FEATURES

Attaches to lower flange of metal beams or purlins

Supports 45° flanges up to 2" long, and 90° flanges up to 1-1/2" high

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 23)

SPECIFICATIONS

Material: Cast Iron

Table 1/2

Catalog Number	Finish	Rod Size (RS)	Flange Thickness (FT)	A	B	Screw Diameter (Sc)
3150037EG	Electrogalvanized	3/8"	1" Max	2"	1 1/2"	3/8"
3150037PL	Plain	3/8"	1" Max	2"	1 1/2"	3/8"

Table 2/2


Catalog Number	Torque (TQ)	Pipe Size	Static Load (F)
3150037EG	5 ft·lbf	4" Max	400lbf
3150037PL	5 ft·lbf	4" Max	400lbf

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Install in accordance with applicable code.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

